



MIRO TR 5VDC SK OPTO-COUPLER MODULE

IN: 5,5 VDC - OUT: 48 VDC / 2 A

Transistor 2 A
5 V DC
Screw terminals

[Link to Product](#)**Illustration**

Product may differ from Image

Approvals

The information in this brochure has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 04/21

**General data**

Test isolation voltage	2.5 kV
Mounting method	DIN-rail mountable (EN 60715)
Housing	Black plastic, flame retardant
Temperature range	-20...+60 °C
Dimensions H×W×D	78×6.2×70 mm

Output

Switching voltage	5...48 V DC
Switching current per output	1 mA...2 A
Saturation voltage (across output)	max. 0.3 V DC
Leakage current (output is open)	max. 10 µA
Switching time ON/OFF	1/5 ms
Switching frequency	max. 10/1 Hz (resist./ind.)

Input

Voltage range ON	4...5.5 V DC
Voltage range OFF	0...2 V DC
Control current	6 mA
LED display	LED (yellow)

Commercial data

country of origin	CZ
customs tariff number	85414090
EAN	4048879026925
eClass	27371604
Packaging unit	1