MURR ELEKTRONIK
stay connected


# POTENTIAL TERMINAL BLOCK BL.YELL.BR.BL

Potential terminal block
blue/yellow/brown/blue

## Link to Product

### Illustration






Product may differ from Image

### Commercial data

| | |
|---|---|
| ECLASS-6.0 | 27141106 |
| ECLASS-6.1 | 27141106 |
| ECLASS-7.0 | 27141106 |
| ECLASS-8.0 | 27141106 |
| ECLASS-9.0 | 27141106 |
| ECLASS-10.1 | 27141106 |
| ECLASS-11.1 | 27141106 |
| ECLASS-12.0 | 27141106 |
| ETIM-5.0 | EC001283 |
| customs tariff number | 85369010 |
| GTIN | 4048879049351 |
| Packaging unit | 1 |

### Electrical data | Supply

| | |
|---|---|
| Operating voltage AC max. | 30 V |
| Operating voltage DC max. | 30 V |
| Total current max. | 10 A |

### Installation

| | |
|---|---|
| Connection cross section max. | 2,5 mm² |
| AWG number min. | 28 |
| AWG number max. | 14 |

### Installation | Connection

| | |
|---|---|
| Connection | Spring clamp plug-in terminals |

### Device protection | Electrical

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-28

| | |
|---|---|
| Degree of protection (EN IEC 60529) | IP20 |
| **Mechanical data \| Mounting data** | |
| Height | 70 mm |
| Width | 56 mm |
| Depth | 32,5 mm |
| **Environmental characteristics \| Climatic** | |
| Operating temperature min. | 0 °C |
| Operating temperature max. | 55 °C |
| Storage temperature min. | -40 °C |
| Storage temperature max. | 85 °C |

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-28