

MVK Fusion

MVK PN FDI6/3 FDO2/1 DIO4 IOL2 IRT PP


Double safety output port
safe inputs/outputs up to cat.4/PLe (EN ISO 13849-1), up to SIL3 (IEC 61508), up to SILCL3 (IEC 62061)
FDI6/3 FDO2/1 DIO4 IOL2 (IRT)
Ethernet 10/100 Mbit/s; Push Pull RJ45 Data connector
Push Pull Power connector, max. 16 A
M12, 5-pole, A-coded
Galvanic isolation
Connection cables are in the online shop under "Connection Technology".
Housing fully potted.

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.1	27242604
ECLASS-7.0	27242604
ECLASS-8.0	27242604
ECLASS-9.0	27242604
ECLASS-10.1	27242604
ECLASS-11.1	27242604
ECLASS-12.0	27242604
customs tariff number	85389099
GTIN	4048879714983
Packaging unit	1
Safety codes	
Service life	20 a
Category (EN ISO 13849-1)	4 (X0, X1, X2, X3); 3 (X7 PIN 3)
PFHd (IEC 61508)	7,8 E-10/h
PFHd (IEC 62061)	48 E-10/h
Performance level (EN ISO 13849-1)	e (X0, X1, X2, X3); d (X7 PIN 3)

SIL (IEC 61508)	3 (X0, X1, X2, X3); 2 (X7 PIN 3)
-----------------	----------------------------------

SIL CL (IEC 62061)	3
--------------------	---

Electrical data | Supply

Norm operating voltage	EN 61131-2
------------------------	------------

Operating voltage US DC	24 V
-------------------------	------

Operating voltage UA DC	24 V
-------------------------	------

Total current US max.	16 A
-----------------------	------

Electrical data | Input

Number of F inputs	6
--------------------	---

Overload resistant	yes
--------------------	-----

Short-circuit protected	yes
-------------------------	-----

Type Safety input	for electronical sensors or mechanical switches
-------------------	---

Type input	PNP, for 3-wire sensors or mechanical switches, IO-Link Devices
------------	---

Sensor current US per input max.	0,7 A
----------------------------------	-------

Current carrying capacity max.	0,7 A
--------------------------------	-------

Electrical data | Output

Switching behavior safety output	2 FDO X3 (PIN 2, PIN 4: pp, pm, ppm switching); 1 FDO X7 (PIN 2: pp switching)
----------------------------------	--

Overload resistant	yes
--------------------	-----

Short-circuit protected	yes
-------------------------	-----

Output current per pin (safety) max.	2 A
--------------------------------------	-----

Output current per pin max.	2 A
-----------------------------	-----

Total current output max.	8 A
---------------------------	-----

Industrial communication

Supported protocol	PROFINET
--------------------	----------

Industrial communication | Profinet

Number of active connections (IO controller) max.	2
---	---

IRT (network communication)	yes
-----------------------------	-----

MRP client	yes
------------	-----

PROFINET Netload Class	III
------------------------	-----

PROFINET addressing	DCP
---------------------	-----

PROFINET conformance class	C
----------------------------	---

PROFINET specification	V2.3
------------------------	------

Shared device/input	yes
---------------------	-----

Industrial communication | IO-Link

Automatic baudrate detection	yes
------------------------------	-----

IO-Link process data length output	32 Bytes
------------------------------------	----------

IO-Link process data length input	32 Bytes
-----------------------------------	----------

IO-Link revision ID	V1.1.2
---------------------	--------

IO-Link type	2x Master
--------------	-----------

IO-Link transmission rate	COM1, COM2, COM3
---------------------------	------------------

Port Class	A, B
------------	------

Diagnostics

Actuator warning	per channel via LED and BUS
------------------	-----------------------------

Diagnostic via BUS	per module and channel
--------------------	------------------------

Diagnostic via LED	per module and channel
--------------------	------------------------

Wire break detection	yes
----------------------	-----

IO-Link events	No voltage, Undervoltage supply
----------------	---------------------------------

Short circuit diagnosis	yes
-------------------------	-----

LED display	Ethernet connection/data traffic
-------------	----------------------------------

Cross-link detection	Sensor/Actuator
----------------------	-----------------

Overload diagnosis	yes
--------------------	-----

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP67
Galvanic separation (operating voltage)	yes

Mechanical data | Mounting data

Suitable for mounting type	2-hole screw mounting
Height	51,2 mm
Width	63 mm
Depth	225 mm

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
Operating temperature max.	60 °C
Storage temperature min.	-40 °C
Storage temperature max.	85 °C

Connection type 7

Connection type 1	X0-X2
Connection type 2	X3
Connection type 3	X4, X5
Connection type 4	X6
Connection type 5	X7
Connection type 6	XD1, XD2
Connection type 7	XF1, XF2
Family construction form	M12
Gender	female
Color contact carrier	yellow
Coding	A
No. of poles	5
PIN 1	24 V DC (US 1) Test Pulse P 4
PIN 2	FDI
PIN 3	0 V (US 1)
PIN 4	FDI
PIN 5	24 V DC (US 1) Test Pulse P 2
Family construction form	M12
Gender	female
Color contact carrier	yellow
Coding	A
No. of poles	5
PIN 1	n.c.
PIN 2	FDO
PIN 3	0 V (US 2)
PIN 4	FDO
PIN 5	n.c.
Family construction form	M12
Gender	female
Color contact carrier	black
Coding	A
No. of poles	5
PIN 1	24 V DC (US 2)
PIN 2	DI / DO
PIN 3	0 V (US 2)
PIN 4	DI / DO
PIN 5	PE
Family construction form	M12
Gender	female

Color contact carrier	gray
Coding	A
No. of poles	5
PIN 1	24 V DC (US 1)
PIN 2	DI
PIN 3	0 V (US 1)
PIN 4	DI / IO-Link
PIN 5	n.c.
Family construction form	M12
Gender	female
Color contact carrier	gray
Coding	A
No. of poles	5
PIN 1	24 V DC (US 1)
PIN 2	DO (US 2)
PIN 3	0 V (US 1)
PIN 4	DI / IO-Link
PIN 5	0 V (US 2)
Family construction form	Push Pull
Gender	male
Color contact carrier	green
No. of poles	5
PIN 1	24 V DC (US 1)
PIN 2	0 V (US 1)
PIN 3	24 V DC (US 2)
PIN 4	0 V (US 2)
PIN 5	PE
Family construction form	RJ45
Gender	female
Color contact carrier	black
No. of poles	8
PIN 1	TD +
PIN 2	TD -
PIN 3	RD +
PIN 4	n.c.
PIN 5	n.c.
PIN 6	RD -
PIN 7	n.c.
PIN 8	n.c.