MASI20 I/O MODULE RELAY

4 digital inputs, 4 digital relay outputs

Art.No.: 56478
Weight: 0.125 kg
Country of origin: SG
Model designation: MASI20 DI4/0,15A DO4R/2,0A AB

Digital inputs/relay outputs
DI4 - 0.15 A DO4R - 2 A (AB)
AB-Slave
Protection IP20
Current manuals can be downloaded at: www.murrelektronik.com

Link to Product

Illustration



Product may differ from Image

Commercial data

URL webshop	https://shop.murrelektronik.com/56478
GTIN	4048879705622
EU-Customs tariff number	85176200
US-Customs tariff number	8517620090
ECLASS-6.0	27242604
ECLASS-6.1	27242604
ECLASS-7.0	27242604
ECLASS-7.1	27242604
ECLASS-8.0	27242604
ECLASS-8.1	27242604
ECLASS-9.0	27242604
ECLASS-9.1	27242604
ECLASS-10.0.1	27242604
ECLASS-10.1	27242604
ECLASS-11.0	27242604
ECLASS-11.1	27242604

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-11-18

ECLASS-12.0	27242604
ECLASS-13.0	27242604
ECLASS-14.0	27242604
ETIM-5.0	EC001599
ETIM-6.0	EC001599
ETIM-7.0	EC001599
ETIM-8.0	EC001599
ETIM-9.0	EC001599
ETIM-10.0	EC001599
customs tariff number	85176200
EAN	4048879705622
Packaging unit	1
Electrical data | Supply	
Total current max.	8 A
Operating voltage external DC min.	12 V
Operating voltage external DC max.	30 V
Bus voltage AS-Interface DC min.	26.5 V
Bus voltage AS-Interface DC max.	31.6 V
Current consumption AS-i port max.	230 mA
Module supply	Via system connection or by additional feed-in
Electrical data | Input	
Input current max.	5.6 mA
Current carrying capacity max.	0.15 A
Short-circuit protected	Yes
Overload resistant	Yes
Input type	For 3-wire sensors or mechanical switches, PNP
Electrical data | Output	
Output voltage AC	250 V
Output voltage DC	30 V
Output current per pin max.	2 A
Industrial communication | Bus data	
Address setting type	Addressing socket, Master
Slave address range	(0), 1 A...31 A, 1 B...31 B
Industrial communication | AS-Interface	
Profile (IO.ID.ID2)	S-7.A.7
Diagnostics	
Diagnostics	No voltage
Diagnostic via LED	Per module
LED display	Ethernet connection/data traffic
Device protection | Electrical	
Degree of protection (EN IEC 60529)	IP20
Mechanical data | Mounting data	
Height	125 mm
Width	19 mm
Depth	99 mm
Mounting method	Snapped
Suitable for mounting type	(EN 60715), Mounting rail
Environmental characteristics | Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	70 °C
Ambient temperature (storage, transport)	-25 °C … 85 °C

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-11-18

Connection type 2-2	
Connection type 1	Asi Bus
Connection type 2	I / O
Family construction form	Terminal
No. of poles	4
Gender	Female
Color contact carrier	yellow
Connection type	Spring clamp terminals FK
PIN 25	AS-i +
PIN 26	AS-i +
PIN 27	AS-i -
PIN 28	AS-i -
Family construction form	Terminal
No. of poles	24
Gender	Female
Color contact carrier	black
Connection type	Spring clamp terminals FK
PIN 1	I 1
PIN 2	I 2
PIN 3	I 3
PIN 4	I 4
PIN 5	I -
PIN 6	I -
PIN 7	I -
PIN 8	I -
PIN 9	I +
PIN 10	I +
PIN 11	I +
PIN 12	I +
PIN 15	O 13
PIN 16	O 14
PIN 17	O 23
PIN 18	O 24
PIN 19	O 33
PIN 20	O 34
PIN 21	O 43
PIN 22	O 44

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-11-18