



**MKS - D 10/1300-1 M DIODE MODULES**

Mounting rail / screw-type terminal

10 diodes  
Common potential anode

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27371010
ECLASS-6.1	27371010
ECLASS-7.0	27371010
ECLASS-8.0	27371010
ECLASS-9.0	27371010
ECLASS-10.1	27371010
ECLASS-11.1	27371010
ECLASS-12.0	27371010

ETIM-5.0	EC002780
customs tariff number	85411000
GTIN	4048879041959
Packaging unit	1
<b>Electrical data   Supply</b>	
Operating voltage AC max.	48 V
Operating voltage DC max.	48 V
<b>Installation</b>	
Connection cross section max.	4 mm <sup>2</sup>
<b>Installation   Connection</b>	
Connection	Screw terminals SK
<b>Mechanical data   Mounting data</b>	
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, G32, (EN 60715)
Height	86 mm
Width	22,5 mm
Depth	62 mm
<b>Environmental characteristics   Climatic</b>	
Operating temperature min.	-20 °C
Operating temperature max.	60 °C
<b>Connection type 1</b>	
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
No. of poles	12