



MB CAP ULTRA BUFFER MODULE

IN: 12/24VDC OUT:12/24VDC/10A for max.1A/380S

INPUT: 24 V DC (SELV/PELV)
OUTPUT: max. 10 A
38 s (10 A); 380 s (1 A)

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27049190
ECLASS-6.1	27049002
ECLASS-7.0	27049002
ECLASS-8.0	27049002
ECLASS-9.0	27040705
ECLASS-10.1	27040705

ECLASS-11.1	27040705
ECLASS-12.0	27040705
ETIM-5.0	EC002584
customs tariff number	85322900
GTIN	4048879079785
Packaging unit	1
Electrical data	
Security level	SELV/PELV
Electrical data Input	
Max. inrush current duration	2 ms
Input voltage 1 DC	12 V
Input voltage 1 DC min.	11,9 V
Input voltage 1 DC max.	15 V
Input voltage 2 DC	24 V
Input voltage 2 DC min.	23,9 V
Current input AC	10 A
Max. inrush current	35 A
Charging time min.	100 s
Charging time max.	210 s
Switching input potential free	27 V
Efficiency	90 %
Electrical data Output	
Output voltage 1 DC	11,3 V
Output voltage 2 DC	23,3 V
Output voltage adjustable	yes
Output current max.	10 A
Mechanical data Mounting data	
Mounting method	geschnappt
Suitable for mounting type	Tragschiene TH35-7.5/TH35-15, (EN 60715)
Environmental characteristics Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	60 °C
Storage temperature min.	-20 °C
Storage temperature max.	60 °C
Conformity	
Product standard	EN 60950, EN 50178