



MKN POWER SUPPLY 1-PHASE, LINEAR REGULATED

IN: 230VAC OUT: 24V/0,07ADC

INPUT: 230 V AC
 OUTPUT: 24 V DC
 Current: 70 mA

This power supply units meet the (EN 61000-3-2) standard for harmonic current.
 Condensation not permitted

[Link to Product](#)**Illustration**

Product may differ from Image

**Commercial data**

ECLASS-6.0	27049002
ECLASS-6.1	27049002
ECLASS-7.0	27049002
ECLASS-8.0	27049002
ECLASS-9.0	27040701

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-05-03

Murrelektronik GmbH | Falkenstraße 3 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

ECLASS-10.1	27040701
ECLASS-11.1	27040701
ECLASS-12.0	27040701
ETIM-5.0	EC002540
customs tariff number	85044095
GTIN	4048879079662
Packaging unit	1

Electrical data | Supply

Power frequency	50 ... 60 Hz
-----------------	--------------

Electrical data | Input

Characteristic back-up fuse	Inertia
Input voltage AC min.	207 V
Input voltage AC max.	253 V
Input current	10 mA
External back-up fuse per phase max.	0,063 A

Electrical data | Output

Output suppression	Screening capacitor, VDR
Output current max.	0,07 A
Ripple (s-s) max.	10 mV

Device protection | Electrical

Overload protection output	yes
Short-circuit protection output	yes

Mechanical data | Mounting data

Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, G32, (EN 60715)

Environmental characteristics | Climatic

Operating temperature min.	0 °C
Operating temperature max.	60 °C

Conformity

Product standard	EN 61558-2-6, EN 62041 category II
EMC	EN 55011 B, EN 61000-3-2