

INTERFACE TERMINAL RELAY

IN: 24 VDC - OUT: 24 VDC / 0.2 A

Transistor 0.2 A  
24 V DC  
Control current 0.1 mA (5 V DC)  
Screw terminals

Link to Product

Illustration



Product may differ from Image



| Commercial data |          |
|-----------------|----------|
| ECLASS-6.0      | 27371604 |
| ECLASS-6.1      | 27371604 |
| ECLASS-7.0      | 27371604 |
| ECLASS-8.0      | 27371604 |
| ECLASS-9.0      | 27371604 |
| ECLASS-10.1     | 27371604 |

|                                                 |                           |
|-------------------------------------------------|---------------------------|
| ECLASS-11.1                                     | 27371604                  |
| ECLASS-12.0                                     | 27371604                  |
| ETIM-5.0                                        | EC001504                  |
| customs tariff number                           | 85414900                  |
| GTIN                                            | 4048879024518             |
| Packaging unit                                  | 1                         |
| <b>Electrical data   Input</b>                  |                           |
| Input voltage OFF DC min.                       | 0 V                       |
| Input voltage OFF DC max.                       | 1,5 V                     |
| Input voltage DC                                | 24 V                      |
| Input voltage DC min.                           | 1,9 V                     |
| Input voltage DC max.                           | 30 V                      |
| Input current DC max.                           | 16 mA                     |
| <b>Electrical data   Output</b>                 |                           |
| Switch off delay max.                           | 20 µs                     |
| Quiescent current OFF max.                      | 0,1 mA                    |
| Switching frequency max.                        | 20000 Hz                  |
| Voltage switching DC min.                       | 5 V                       |
| Switching voltage DC max.                       | 48 V                      |
| Switching current min.                          | 0,1 mA                    |
| Switching current max.                          | 0,2 A                     |
| Voltage drop DC max.                            | 1,2 V                     |
| <b>Diagnostics</b>                              |                           |
| Status indication LED                           | yellow                    |
| <b>Device protection   Electrical</b>           |                           |
| Rated insulation voltage                        | 3750 V                    |
| <b>Device protection   Media</b>                |                           |
| Flame resistance                                | flame retardant           |
| <b>Mechanical data   Material data</b>          |                           |
| Color housing                                   | black                     |
| Material housing                                | Plastic                   |
| <b>Mechanical data   Mounting data</b>          |                           |
| Mounting method                                 | geschnappt                |
| Suitable for mounting type                      | mounting rail, (EN 60715) |
| Height                                          | 91 mm                     |
| Width                                           | 6,2 mm                    |
| Depth                                           | 71 mm                     |
| <b>Environmental characteristics   Climatic</b> |                           |
| Operating temperature min.                      | -20 °C                    |
| Operating temperature max.                      | 60 °C                     |
| Storage temperature min.                        | -40 °C                    |
| Storage temperature max.                        | 80 °C                     |
| <b>Connection type 5</b>                        |                           |
| Connection                                      | Screw terminals SK        |
| Family construction form                        | terminal                  |
| Gender                                          | female                    |
| Color contact carrier                           | black                     |
| No. of poles                                    | 1                         |
| PIN 1                                           | -                         |
| Connection                                      | Screw terminals SK        |
| Family construction form                        | terminal                  |

|                          |                    |
|--------------------------|--------------------|
| Gender                   | female             |
| Color contact carrier    | black              |
| No. of poles             | 1                  |
| PIN 1                    | +                  |
| Connection               | Screw terminals SK |
| Family construction form | terminal           |
| Gender                   | female             |
| Color contact carrier    | black              |
| No. of poles             | 1                  |
| PIN 1                    | In                 |
| Connection               | Screw terminals SK |
| Family construction form | terminal           |
| Gender                   | female             |
| Color contact carrier    | black              |
| No. of poles             | 1                  |
| PIN 1                    | 14                 |
| Connection               | Screw terminals SK |
| Family construction form | terminal           |
| Gender                   | female             |
| Color contact carrier    | black              |
| No. of poles             | 1                  |
| PIN 1                    | 13 +               |