

Discontinued since 27 April 2020

Last order 30 November 2020


INPUT: 100...240 V AC; 120...370 V DC

OUTPUT: 24...28 V DC

Current: 0.42 A

Spring clamp plug-in terminal: 0.2...2.5 mm²[Link to Product](#)**Illustration**

Product may differ from Image

**Commercial data**

ECLASS-6.0	27049002
ECLASS-7.0	27049002
ECLASS-8.0	27049002
ECLASS-9.0	27040701
ETIM-5.0	EC002540
customs tariff number	85044095
GTIN	4048879299435
Packaging unit	1

Electrical data

Number of devices parallel connection max.	5
Number of devices series connection max.	2
Parallel connection	yes
Series connection	yes
Security level	SELV

Electrical data | Supply

Power frequency	50 ... 60 Hz
-----------------	--------------

Electrical data | Input

Input voltage 1 AC	115 V
Input voltage 2 AC	230 V
Input voltage AC min.	100 V
Input voltage AC max.	240 V
Input voltage DC min.	120 V
Input voltage DC max.	370 V
Input current at input voltage 1 AC	0,2 A

Input current at input voltage 2 AC	0,12 A
Inrush current max.	30 A
External back-up fuse per phase max.	10 A
Efficiency	86 % @ 110 V AC, 88 % @ 230 V AC

Electrical data | Output

Output voltage DC	24 V
Output voltage DC min.	24 V
Output voltage DC max.	28 V
Output voltage adjustable	yes
Output current	0,42 A
Mains failure bridging min.	10 ms @ 115 V AC
Mains failure bridging max.	25 ms @ 115 V AC
Ripple effective max.	20 mV
Spikes (s-s) max.	100 mV

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP20
Overload protection output	yes
Short-circuit protection output	yes

Mechanical data | Mounting data

Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)

Environmental characteristics | Climatic

Operating temperature min.	0 °C
Operating temperature max.	50 °C
Derating from	50 °C
Storage temperature min.	-25 °C
Storage temperature max.	85 °C
Relative humidity min. (operation)	20 %
Relative humidity max. (operation)	90 % no condensation

Conformity

Product standard	IEC 61010-2-201
EMC	EN 55022 B, EN 61000-3-2
Low Voltage Directive	EN 61204-3