

Cube67 Valve-Interface, Compact Module

DO16, SMC SV/VQ, Sub-D 25 pol., 0,6m, 4x U Act.


Compact module  
DO16 Valve (C) - 4x U-Actuator 0.5 m  
Multipole plug (0.5 A)  
SMC - Series SV/VQ  
Connection cables are in the online shop under "Connection Technology".  
Housing fully potted.

Link to Product

Illustration



Product may differ from Image



| Commercial data          |               |
|--------------------------|---------------|
| ECLASS-6.0               | 27242604      |
| ECLASS-6.1               | 27242604      |
| ECLASS-7.0               | 27242604      |
| ECLASS-8.0               | 27242604      |
| ECLASS-9.0               | 27242604      |
| ECLASS-10.1              | 27242604      |
| ECLASS-11.1              | 27242604      |
| ECLASS-12.0              | 27242604      |
| ETIM-5.0                 | EC001599      |
| customs tariff number    | 85389099      |
| GTIN                     | 4048879306218 |
| Packaging unit           | 1             |
| Electrical data   Supply |               |
| Norm operating voltage   | EN 61131-2    |
| Operating voltage UA DC  | 24 V          |
| Current consumption max. | 50 mA         |
| Total current UA max.    | 4 A           |
| Total current US max.    | 4 A           |
| Electrical data   Output |               |

|                             |       |
|-----------------------------|-------|
| Overload resistant          | yes   |
| Short-circuit protected     | yes   |
| Output current per pin max. | 0,5 A |

#### Diagnostics

|                         |                                  |
|-------------------------|----------------------------------|
| Actuator warning        | per channel via BUS              |
| Diagnostic              | No voltage, Under voltage        |
| Diagnostic via BUS      | per module and channel           |
| Diagnostic via LED      | per module                       |
| Short circuit diagnosis | yes                              |
| LED display             | Ethernet connection/data traffic |
| Overload diagnosis      | yes                              |

#### Device protection | Electrical

|                                     |      |
|-------------------------------------|------|
| Degree of protection (EN IEC 60529) | IP67 |
|-------------------------------------|------|

#### Mechanical data | Mounting data

|                            |                       |
|----------------------------|-----------------------|
| Suitable for mounting type | 2-hole screw mounting |
| Height                     | 150 mm                |
| Width                      | 30 mm                 |
| Depth                      | 34,5 mm               |

#### Environmental characteristics | Climatic

|                            |        |
|----------------------------|--------|
| Operating temperature min. | 0 °C   |
| Operating temperature max. | 55 °C  |
| Storage temperature min.   | -20 °C |
| Storage temperature max.   | 70 °C  |

#### Connection type 3

|                          |              |
|--------------------------|--------------|
| Connection type 1        | Bus In       |
| Connection type 2        | Data         |
| Connection type 3        | Power In     |
| Family construction form | M12          |
| Gender                   | male         |
| Color contact carrier    | black        |
| Coding                   | A            |
| No. of poles             | 6            |
| PIN 1                    | 24 V DC (UA) |
| PIN 2                    | 24 V DC (US) |
| PIN 3                    | 0 V          |
| PIN 4                    | Bus internal |
| PIN 5                    | Bus internal |
| PIN 6                    | 0 V          |
| Family construction form | D-Sub        |
| Gender                   | male         |
| No. of poles             | 25           |
| PIN 1                    | Out 1        |
| PIN 2                    | Out 3        |
| PIN 3                    | Out 5        |
| PIN 4                    | Out 7        |
| PIN 5                    | Out 9        |
| PIN 6                    | Out 11       |
| PIN 7                    | Out 13       |
| PIN 8                    | Out 15       |
| PIN 13                   | 0 V          |
| PIN 14                   | Out 2        |
| PIN 15                   | Out 4        |

|                          |                |
|--------------------------|----------------|
| PIN 16                   | Out 6          |
| PIN 17                   | Out 8          |
| PIN 18                   | Out 10         |
| PIN 19                   | Out 12         |
| PIN 20                   | Out 14         |
| PIN 21                   | Out 16         |
| Family construction form | M12            |
| Gender                   | male           |
| Color contact carrier    | black          |
| Coding                   | A              |
| No. of poles             | 6              |
| PIN 1                    | 24 V DC (UA 1) |
| PIN 2                    | 24 V DC (UA 2) |
| PIN 3                    | 0 V            |
| PIN 4                    | 24 V DC (UA 3) |
| PIN 5                    | 24 V DC (UA 4) |
| PIN 6                    | 0 V            |