

**MIRO 6.2 PLUGGABLE PLUG IN MODULE OUTPUT RELAY**


IN: 24 VDC - OUT: 250 VAC/DC / 6 A

Art.No.: 3000-16023-2100010

Weight: 0.005

Country of origin: CZ

Model designation: Ausgrel. 24V/230V 6A (Steckmodul)

[Link to Product](#)**Illustration**

Product may differ from Image

**Commercial data**

ECLASS-6.0	27371601
ECLASS-6.1	27371601
ECLASS-7.0	27371601
ECLASS-8.0	27371601
ECLASS-9.0	27371601
ECLASS-10.1	27371601
ECLASS-11.1	27371601
ECLASS-12.0	27371601
ETIM-5.0	EC001437
ETIM-6.0	EC001437
ETIM-7.0	EC001437
ETIM-8.0	EC001437
customs tariff number	85364900
customs tariff number	85364900
EAN	4048879021371
EAN	4048879021371
Packaging unit	1
Packaging unit	1

**Electrical data | Input**

Input voltage AC	24 V
Input voltage DC	24 V

**Electrical data | Output**

Power rating AC max.	1500 VA
Power rating DC max.	120 W
Switching voltage AC max.	250 V
Switching voltage DC max.	30 V

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-05-24

Murrelektronik GmbH | Grabenstraße 29 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

Switching current DC	10 mA
----------------------	-------

Switching current max.	6 A
------------------------	-----

**Device protection | Electrical**

Rated insulation voltage	300 V
--------------------------	-------

**Mechanical data**

Drop-out time max.	4 ms
--------------------	------

Response time max.	8 ms
--------------------	------

**Mechanical data | Material data**

Material contact	Ag Sn O <sub>2</sub>
------------------	----------------------

**Mechanical data | Mounting data**

Mounting method	inserted
-----------------	----------

**Environmental characteristics | Climatic**

Operating temperature min.	-40 °C
----------------------------	--------

Operating temperature max.	60 °C
----------------------------	-------

Storage temperature min.	-40 °C
--------------------------	--------

Storage temperature max.	60 °C
--------------------------	-------