

MODLINK MSDD DATA INSERT

2×USB-A female/female + 1×RJ45 + 1×RJ12

RJ45; RJ12; USB; USB (A)
1× RJ45, 8-pole metal, CAT5e (female/female)
1× RJ12 (6-pole plastic)
2× USB (female/female) form A

Link to Product

Illustration



Product may differ from Image



Commercial data

ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27189217
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC002625
customs tariff number	85366990
GTIN	4048879037839
Packaging unit	1

Mechanical data | Mounting data

Height	88 mm
Width	51 mm
Depth	70,4 mm

Environmental characteristics | Climatic

Storage temperature min.	-10 °C
Storage temperature max.	60 °C

Shielding plate

Connection information Threaded hole M4

Tightening torque 0,9 Nm

USB

Operating voltage AC 48 V

Operating voltage DC 48 V

Operating voltage AC max. (UL-listed) 30 V

Operating voltage DC max. (UL-listed) 42,4 V

Operating current 1,5 A

USB specification 3.0

Data transmission rate max. 5000 MBit/s

Looking techniques Snap-in connector

RJ12

Operating voltage AC max. 48 V

Operating voltage DC max. 48 V

Operating voltage AC max. (UL-listed) 30 V

Operating voltage DC max. (UL-listed) 42,4 V

Operating current max. 1 A

Current operating max. (UL) 175 mA

Family construction form RJ12

Family type Back side RJ12

Looking techniques Snap-in connector

RJ45

Operating voltage AC max. (UL-listed) 30 V

Operating voltage DC max. (UL-listed) 42,4 V

Current operating max. (UL) 175 mA

Family construction form RJ45

Family type Back side RJ45

Cable category min. Cat5e

Looking techniques Snap-in connector