M12 female 90° A-cod. with cable shielded

PUR 5x0.34 shielded gy 5m

Art.No.: 7000-13281-3490500
Weight: 0.316 kg
Country of origin: CZ
Model designation: MSDL0-U349_5.0-ZE

Advantages of our connectors:

Our connectors are versatile and specially optimised for industrial environments. All connectors are 100% tested during the manufacturing process to ensure the highest quality and reliability.

The contacts are gold-plated, which ensures optimum conductivity. Thanks to the high degree of protection, the connectors are ideal for demanding industrial environments. They are also vibration-resistant - this is ensured by the union nut with vibration protection.

Our connectors are resistant to oils and cooling lubricants, but resistance to aggressive media should be tested for each specific application. Different cable lengths available on request

If you are missing technical information? Please feel free to use our dictionary to find more technical details.

Product details:

Female 90°
M12, 5-pole
Shielded
With cable grommet
Plastic housings with good resistance against chemicals and oils.
The resistance to aggressive media should be individually tested for your application. Further details on request.
Further cable lengths on request.

Link to Product

Illustration





The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-11-18









Product may differ from Image

Cable length	5,00 m
Side 1-1	
Family construction form	M12
No. of poles	5
Coding	A
Gender	Female
Mounting method	Inserted, Screwed
Thread	M12x1
Tightening torque	0.6 Nm
Width across flats	SW 13
Cable outlet	angled
Material	PUR
Material contact	Copper alloy
Coating contact	Gold plated
Degree of protection (EN IEC 60529)	IP67, IP66K, IP65
Side 2-2	
Family construction form	free cable end
Stripping length (jacket)	20 mm

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-11-18

Commercial data	
URL webshop	https://shop.murrelektronik.com/7000-13281-3490500
EU-Customs tariff number	85444290
US-Customs tariff number	8544429090
ETIM-9.0	EC001855
ETIM-10.0	EC001855
customs tariff number	85444290
EAN	4048879198905
Packaging unit	1
Electrical data | Supply	
Operating voltage AC max.	60 V
Operating voltage DC max.	60 V
Current operating per contact max.	4 A
Diagnostics	
Status indication LED	No
Installation | Connection	
Mounting thread	M12x1
Device protection | Electrical	
Additional condition degree of protection	Inserted, Screwed
Pollution degree	3
Rated surge voltage	1.5 kV
Insulating material group (IEC 60664-1)	I
Mechanical data	
Contour for corrugated hose	without
Mechanical data | Material data	
Screw connection	Zinc die-casting
Coating of fitting	Nickel plated
Gasket	FKM
Mechanical data | Mounting data	
Mounting method	Inserted, Screwed, Shaking protection
Environmental characteristics | Climatic	
Operating temperature min.	-30 °C
Operating temperature max.	85 °C
Additional condition temperature range	Depending on connected cable
Important installation notes	
Note on bending radius	**Attention:** Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
Conformity	
Product standard	EN IEC 61076-2-101 (M12)
Installation | Cable-1	
Cable identification	349
Cable weigth	54 g/m
Stranding	1 Wires
Cable shielding (type)	Copper braid, tinned
Cable shielding (coverage)	85 %
Banding	Nonwoven, Foil
Filler	Yes
Wire arrangement	BN, BK, BU, WH, GNYE
Shielding	Shielded

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-11-18

Material wire insulation	PVC
Amount wires	5
Outer diameter wire insulation	1.45 mm ± 0.05 mm
Conductor crosssection (wire)	0.34 mm²
Material conductor wire	Stranded copper wire, bare
Core construction (wire)	42 × 0.1 mm
Material properties wire insulation	Good machinability
Ingredient freeness wire insulation	Lead-free, Cadmium-free, CFC-free, Silicone-free
Material jacket	PUR
Outer-diameter (jacket)	5.9 mm ± 5 %
Jacket color	gray / RAL 7001
Material inner jacket	PVC
Color (inner jacket)	gray
Freedom from ingredients (jacket)	Lead-free, Cadmium-free, CFC-free, Halogen-free
Material property (jacket)	Abrasion-resistant, Low adhesion, Good machinability, Matte
Cable shielding (type)	Copper braid, tinned
Cable shielding (coverage)	85 %
Conductor resistance (wire)	57 Ω/km @ 20 °C
Current load capacity (standard)	To DIN VDE 0298-4
Current load capacity max. (wire)	4.5 A
Max. rated voltage (conductor - conductor)	350 V
Max. rated voltage (conductor - ground)	300 V
Withstand voltage (wire - wire)	2 kV @ 60 s
Withstand voltage (wire - jacket)	2 kV @ 60 s
Withstand voltage (wire - shield)	1.5 kV @ 60 s
Operating temperature (static)	-40 °C … 80 °C
Operating temperature (dynamic)	-5 °C … 70 °C
Other resistances	Hydrolysis-resistant, Microbe-resistant
Notes	Application-related testing
Bending radius (fixed)	10 × Outer diameter
Bending radius (dynamic)	15 × Outer diameter
No. of bending cycles (C-track)	0.1 Mio. @ 25 °C
Traversing distance (C-track)	5 m @ 25 °C
Travel speed (C-track)	3 m/s @ 25 °C
Acceleration (C-track)	3 m/s² @ 25 °C

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-11-18