

M12 FEMALE 0° B CODED SHIELDED WIREABLE SCREW TERM.5 POLE max. 0.75mm² 6-8mm PROFIBUS

Female straight

M12, 5-pole

B-coded

shielded


Screw terminals

Sealing range (cable Ø): 6...8 mm

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)**Illustration**

Female



Product may differ from Image

Approvals**More Info****Form**

Form 14021

General data



Pollution Degree	3
Dimensions H×W×D	57×20×20 mm
Temperature range	-40...+85 °C
Material (gasket)	FKM

Technical Data

Operating voltage	max. 60 V AC/DC
Rated surge voltage	1.5 kV
Operating current per contact	max. 4 A
Material group	IEC 60664-1, category II
Connection cross section	max. 0.75 mm ²
Coding	B-coded
Sealing range (cable Ø)	6...8 mm
Locking of ports	Screw thread (M12×1 mm) recommended torque 0.6 Nm, self-securing
Protection	IP67 inserted and tightened (EN 60529)
Locking material	Zinc die casting, matte nickel plated
Housing	Zinc die casting, matte nickel plated

Commercial data

country of origin	DE
customs tariff number	85366990
EAN	4048879198622
eClass	27279221
Packaging unit	1

Sketch

Product may differ from Image