M12 female 0° A-cod. screw terminal

5-pol., max. 0,75mm², 6 - 8mm, shielded

Art.No.: 7000-13401-0000000
Weight: 0.048 kg
Country of origin: HU
Model designation: M12 BUCHSE GER.6...8 5pol.

Female straight
M12, 5-pole
A-coded
shielded

Link to Product

Illustration







Product may differ from Image

Side 1

Family construction form	M12
Degree of protection (EN IEC 60529)	IP67

Commercial data

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-09-10

ECLASS-6.0	27279221
ECLASS-6.1	27260702
ECLASS-7.0	27440102
ECLASS-8.0	27440102
ECLASS-9.0	27440116
ECLASS-10.1	27440102
ECLASS-11.1	27440102
ECLASS-12.0	27440116
ETIM-5.0	EC002635
customs tariff number	85366990
EAN	4048879198790
Packaging unit	1
Electrical data | Supply	
Operating voltage AC max.	60 V
Operating voltage DC max.	60 V
Current operating per contact max.	4 A
Installation	
Connection cross section max.	0,75 mm²
Device protection | Electrical	
Additional condition protection degree	inserted, screwed
Mechanical data | Material data	
Material housing	Brass
Coating housing	nickel plated
Mechanical data | Mounting data	
Clamping range min.	6 mm
Clamping range max.	8 mm
Environmental characteristics | Climatic	
Operating temperature min.	-40 °C
Operating temperature max.	85 °C
Important installation notes	
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
Note on bending radius	**Attention:** Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-09-10