

M12 female 0° B-cod. with cable

PUR 5x0.34 ye UL/CSA+drag ch. 15m

Female straight  
M12, 5-pole  
B-coded  
Art-No. 7005 - M12 Lite - (plastic hexagonal screw) on request  
Plastic housings with good resistance against chemicals and oils.  
The resistance to aggressive media should be individually tested for your application. Further details on request.  
Further cable lengths on request.

Link to Product

Illustration



Product may differ from Image



Cable length 15 m

Side 1

Tightening torque 0,6 Nm

|                                           |                   |
|-------------------------------------------|-------------------|
| Mounting method                           | inserted, screwed |
| Coating contact                           | gold plated       |
| Family construction form                  | M12               |
| Thread                                    | M12 x 1           |
| suitable for corrugated tube (internal Ø) | 10 mm             |
| Coding                                    | B                 |
| Material contact                          | Copper alloy      |
| Material                                  | PUR               |
| No. of poles                              | 5                 |
| Width across flats                        | SW13              |
| Degree of protection (EN IEC 60529)       | IP65, IP66K, IP67 |

**Side 2**

|                 |             |
|-----------------|-------------|
| Coating contact | gold plated |
|-----------------|-------------|

**Commercial data**

|                       |               |
|-----------------------|---------------|
| ECLASS-6.0            | 27061801      |
| ECLASS-6.1            | 27279218      |
| ECLASS-7.0            | 27279218      |
| ECLASS-8.0            | 27279218      |
| ECLASS-9.0            | 27060311      |
| ECLASS-10.1           | 27060311      |
| ECLASS-11.1           | 27060311      |
| ECLASS-12.0           | 27060311      |
| ETIM-5.0              | EC001855      |
| customs tariff number | 85444290      |
| GTIN                  | 4048879777018 |
| Packaging unit        | 1             |

**Electrical data | Supply**

|                                    |       |
|------------------------------------|-------|
| Operating voltage AC max.          | 125 V |
| Operating voltage DC max.          | 125 V |
| Current operating per contact max. | 4 A   |

**Diagnostics**

|                       |    |
|-----------------------|----|
| Status indication LED | no |
|-----------------------|----|

**Installation | Connection**

|              |         |
|--------------|---------|
| Mounting set | M12 x 1 |
|--------------|---------|

**Device protection | Electrical**

|                                        |                   |
|----------------------------------------|-------------------|
| Additional condition protection degree | inserted, screwed |
| Pollution Degree                       | 3                 |
| Rated surge voltage                    | 1,5 kV            |
| Material group (IEC 60664-1)           | I                 |

**Mechanical data | Material data**

|                           |                  |
|---------------------------|------------------|
| Coating locking           | Nickeled         |
| Coating of fitting        | nickel plated    |
| Material gasket           | FKM              |
| Locking material          | Zinc die-casting |
| Material screw connection | Zinc die-casting |

**Mechanical data | Mounting data**

|                 |                                       |
|-----------------|---------------------------------------|
| Mounting method | inserted, screwed, Shaking protection |
|-----------------|---------------------------------------|

**Environmental characteristics | Climatic**

|                                        |                            |
|----------------------------------------|----------------------------|
| Operating temperature min.             | -25 °C                     |
| Operating temperature max.             | 85 °C                      |
| Additional condition temperature range | depending on cable quality |

| Important installation notes                      |                                                                                                                                                       |
|---------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|
| Note on strain relief                             | Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.                                                   |
| Note on bending radius                            | <b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces. |
| Conformity                                        |                                                                                                                                                       |
| Product standard                                  | DIN EN 61076-2-101 (M12)                                                                                                                              |
| Installation   Cable                              |                                                                                                                                                       |
| wire arrangement                                  | brown, black, blue, white, green-yellow                                                                                                               |
| Cable identification                              | 035                                                                                                                                                   |
| Cable Type                                        | 3                                                                                                                                                     |
| Jacket Color                                      | yellow                                                                                                                                                |
| Type of Certificate                               | cURus                                                                                                                                                 |
| Amount stranding                                  | 1                                                                                                                                                     |
| Stranding                                         | 5 wires around Core filler twisted                                                                                                                    |
| Filler                                            | yes                                                                                                                                                   |
| wire arrangement                                  | brown, black, blue, white, green-yellow                                                                                                               |
| Cable weight                                      | 41,8 g/m                                                                                                                                              |
| Material jacket                                   | PUR                                                                                                                                                   |
| Shore hardness jacket                             | 90 ± 5 Shore A                                                                                                                                        |
| Freedom from ingredients (jacket)                 | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free                                                                                        |
| Outer-diameter (jacket)                           | 4,8 mm                                                                                                                                                |
| Tolerance outer diameter (sheath)                 | ± 5 %                                                                                                                                                 |
| Material wire insulation                          | PP                                                                                                                                                    |
| Amount wires                                      | 5                                                                                                                                                     |
| Outer diameter insulation                         | 1,25 mm                                                                                                                                               |
| Outer diameter tolerance core insulation          | ± 5 %                                                                                                                                                 |
| Shore hardness wire insulation                    | 70 ± 5 Shore D                                                                                                                                        |
| Ingredient freeness wire insulation               | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free                                                                                        |
| Amount strands (wire)                             | 42                                                                                                                                                    |
| Diameter of single wires                          | 0,1 mm                                                                                                                                                |
| Conductor crosssection (wire)                     | 0,34 mm <sup>2</sup>                                                                                                                                  |
| Material conductor wire                           | Stranded copper wire, bare                                                                                                                            |
| Conductor type (wire)                             | strand class 6                                                                                                                                        |
| Nominal voltage AC max.                           | 300 V                                                                                                                                                 |
| Current load capacity (standard)                  | to DIN VDE 0298-4                                                                                                                                     |
| Current load capacity min. wire                   | 4,5 A                                                                                                                                                 |
| Electrical resistance line constant wire          | 57 Ω/km @ 20 °C                                                                                                                                       |
| AC withstand voltage (wire - wire)                | 2,5 kV @ 60 s                                                                                                                                         |
| Power frequency withstand voltage (wire - jacket) | 2,5 kV @ 60 s                                                                                                                                         |
| Min. operating temperature (static)               | -40 °C                                                                                                                                                |
| Max. operating temperature (fixed)                | 80 °C / 90 °C @ 10000 h Operation                                                                                                                     |
| Operating temperature min. (dynamic)              | -25 °C                                                                                                                                                |
| Operating temperature max. (dynamic)              | 80 °C / 90 °C @ 10000 h Operation                                                                                                                     |
| Flame resistance                                  | UL 1581 § 1100 FT2   IEC 60332-2-2   UL 1581 § 1090                                                                                                   |
| chemical resistance                               | Good, application-related testing                                                                                                                     |
| Gasoline resistance                               | Good, application-related testing                                                                                                                     |
| Oil resistance                                    | DIN EN 60811-404   Good, application-related testing                                                                                                  |
| Bending radius (fixed)                            | 5 x Outer diameter                                                                                                                                    |
| Bending radius (dynamic)                          | 10 x Outer diameter                                                                                                                                   |
| No. of bending cycles (C-track)                   | 10 Mio. @ 25 °C                                                                                                                                       |
| Traversing distance (C-track)                     | 10 m @ 25 °C   horizontal                                                                                                                             |
| Travel speed (C-track)                            | 3 m/s @ 25 °C                                                                                                                                         |
| No. of torsion cycles                             | 2 Mio.                                                                                                                                                |

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-05-22

Murrelektronik GmbH | Falkenstraße 3 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

|                |                                    |
|----------------|------------------------------------|
| Torsion stress | $\pm 180\text{ }^{\circ}/\text{m}$ |
| Torsion speed  | 35 cycles/min                      |