MURR ELEKTRONIK
stay connected

M12 male 90° D-cod. screw terminal


4-pol., max. 0,75mm², 6 - 8mm, shielded


Ethernet CAT5
Male 90°
M12, 4-pole
D-coded
shielded
Screw terminals
Sealing range (cable Ø): 6...8 mm


Link to Product

Illustration









Product may differ from Image

Side 1

Family construction form	M12
Coding	D
Degree of protection (EN IEC 60529)	IP67

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-29

MURR ELEKTRONIK
stay connected

Commercial data	
ECLASS-6.0	27279221
ECLASS-7.0	27440104
ECLASS-8.0	27440104
ECLASS-9.0	27440102
ECLASS-10.1	27440102
ECLASS-11.1	27440102
ECLASS-12.0	27440116
ETIM-5.0	EC002635
customs tariff number	85366990
GTIN	4048879282895
Packaging unit	1
Electrical data | Supply	
Operating voltage AC max.	250 V
Operating voltage DC max.	250 V
Current operating per contact max.	4 A
Industrial communication	
Transfer parameters	CAT5, Class D (ISO/IEC 11801:2002), (EN 50173-1)
Data transmission rate max.	100 MBit/s
Industrial communication | Ethernet functionality	
duplex	Full duplex
Installation	
Connection cross section max.	0,75 mm²
Device protection | Electrical	
Additional condition protection degree	inserted, screwed
Mechanical data | Material data	
Coating locking	Nickeled
Locking material	Zinc die-casting
Mechanical data | Mounting data	
Clamping range min.	6 mm
Clamping range max.	8 mm
Environmental characteristics | Climatic	
Operating temperature min.	-40 °C
Operating temperature max.	85 °C

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-29