

SVS VALVE PLUG FORM B 10 MM FIELD-WIREABLE




24V LED+RC PG9

Form B (10 mm)
24 V AC/DC ±25%
LED and RC
PG9

Plastic housings with good resistance against chemicals and oils.
The resistance to aggressive media should be individually tested for your application. Further details on request.

Link to Product

Illustration



Product may differ from Image

| Side 1 | |
|-------------------------------------|----------|
| Degree of protection (EN IEC 60529) | IP65 |
| Commercial data | |
| ECLASS-6.0 | 27279221 |
| ECLASS-7.0 | 27440104 |
| ECLASS-8.0 | 27440104 |
| ECLASS-9.0 | 27440102 |
| ETIM-5.0 | EC002062 |
| customs tariff number | 85366990 |

| | |
|------|---------------|
| GTIN | 4048879187312 |
|------|---------------|

| | |
|----------------|---|
| Packaging unit | 1 |
|----------------|---|

Electrical data | Supply

| | |
|----------------------|------|
| Operating voltage AC | 24 V |
|----------------------|------|

| | |
|---------------------------|------|
| Operating voltage AC min. | 18 V |
|---------------------------|------|

| | |
|---------------------------|------|
| Operating voltage AC max. | 30 V |
|---------------------------|------|

| | |
|----------------------|------|
| Operating voltage DC | 24 V |
|----------------------|------|

| | |
|---------------------------|------|
| Operating voltage DC min. | 18 V |
|---------------------------|------|

| | |
|---------------------------|------|
| Operating voltage DC max. | 30 V |
|---------------------------|------|

| | |
|------------------------------------|-----|
| Current operating per contact max. | 2 A |
|------------------------------------|-----|

Installation | Connection

| | |
|-------------------|--------|
| Tightening torque | 0,4 Nm |
|-------------------|--------|

| | |
|--------------|----|
| Mounting set | M3 |
|--------------|----|

Installation | Pin assignment

| | |
|--------------|--------|
| No. of poles | 2 + PE |
|--------------|--------|

Device protection | Electrical

| | |
|--|-------------------|
| Additional condition protection degree | inserted, screwed |
|--|-------------------|

Environmental characteristics | Climatic

| | |
|----------------------------|--------|
| Operating temperature min. | -20 °C |
|----------------------------|--------|

| | |
|----------------------------|-------|
| Operating temperature max. | 60 °C |
|----------------------------|-------|