SVS VALVE PLUG FORM BI 11MM FIELD-WIREABLE

230V LED+VDR M16x1.5

Art.No.: 7000-29961-0000000
Weight: 0.050 kg
Country of origin: CN
Model designation: MSVS-KB*X-M16-YS

Form BI (11 mm)
230 V AC/DC ±10%
LED and RC
metric
Plastic housings with good resistance against chemicals and oils.
The resistance to aggressive media should be individually tested for your application. Further details on request.

Link to Product

Illustration







The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-11-18



Product may differ from Image

Side 1-1	
Family construction form	Valve connector form BI
Mounting method	pluggable, Screwed
Degree of protection (EN IEC 60529)	IP65
Commercial data	
URL webshop	https://shop.murrelektronik.com/7000-29961-0000000
EU-Customs tariff number	85366990
US-Customs tariff number	8536694020
ETIM-9.0	EC002635
ETIM-10.0	EC002635
customs tariff number	85366990
EAN	4048879187077
Packaging unit	1
Electrical data	
Drop-out delay time max.	15 ms
Holding power max.	50 W
Electrical data | Supply	
Operating voltage AC	230 V
Operating voltage AC min.	207 V
Operating voltage AC max.	253 V
Operating voltage DC	230 V
Operating voltage DC min.	207 V
Operating voltage DC max.	253 V
Current operating per contact max.	1 A
Cut-off peak voltage max.	450 V
Current consumption max.	12 mA
Diagnostics	
Status indication LED	yellow
Installation	
Connection cross section max.	1.5 mm²
Installation | Connection	
Tightening torque	0.4 Nm

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-11-18

Mounting thread	M16x1,5
Device protection | Electrical	
Additional condition degree of protection	Locked, With screw connection, Inserted
Mechanical data | Mounting data	
Fastening screw	M3x31
Clamping range min.	5 mm
Clamping range max.	10 mm
Environmental characteristics | Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	60 °C
Important installation notes	
Note on bending radius	**Attention:** Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-11-18