SVS Eco valve plug C-8mm screw terminal

2-pol. + PE, max. 0,5mm², 4 -6mm

Art.No.: 7000-30055-0000000
Weight: 0.013 kg
Country of origin: HU
Model designation: MSVSE-DB5K-M12 SVS Eco

Form C (8 mm)
250 V AC/DC
without components
metric
Field-wireable
Plastic housings with good resistance against chemicals and oils.
The resistance to aggressive media should be individually tested for your application. Further details on request.

Link to Product

Illustration







The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-11-18





Product may differ from Image

Side 1-1	
Family construction form	Valve connector form C
Mounting method	pluggable, Screwed
Degree of protection (EN IEC 60529)	IP65
Commercial data	
URL webshop	https://shop.murrelektronik.com/7000-30055-0000000
EU-Customs tariff number	85366990
US-Customs tariff number	8536694020
ETIM-9.0	EC002635
ETIM-10.0	EC002635
customs tariff number	85366990
EAN	4048879187015
Packaging unit	1
Electrical data | Supply	
Operating voltage AC max.	250 V
Operating voltage DC max.	250 V
Current operating per contact max.	6 A
Installation	
Connection cross section max.	0.5 mm²
Installation | Connection	
Tightening torque	0.4 Nm
Tightening torque tolerance	± 0.1 Nm
Tightening torque clamping screw	0.2 Nm
Mounting thread	M12x1,5
Installation | Pin assignment	
No. of poles	2 + PE
Device protection | Electrical	
Additional condition degree of protection	Inserted, Screwed
Mechanical data | Material data	
Gasket	NBR
Mechanical data | Mounting data	
Fastening screw	M2,5
Clamping range min.	4 mm
Clamping range max.	6 mm
Environmental characteristics | Climatic	

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-11-18

Operating temperature min.	-40 °C
Operating temperature max.	90 °C
Important installation notes	
Note on bending radius	**Attention:** Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-11-18