

**M12 male 0° / M12 female 0° A-cod.**

PUR 5x0.34 gy UL/CSA 12m

**⚠ NOTICE ⚠****PRODUCT IS DISCONTINUED. PLEASE HAVE A LOOK AT THE ALTERNATIVE PRODUCTS.**

Male straight – female straight

M12 – M12, 5-pole




A-coded

Art-No. 7005 - M12 Lite - (plastic hexagonal screw) on request


Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

Further cable lengths on request.

[Link to Product](#)**Illustration**

(\* for cable type 126, 732, 219, 619)





Product may differ from Image



|                                           |                   |
|-------------------------------------------|-------------------|
| Cable length                              | 12 m              |
| Side 1                                    |                   |
| Tightening torque                         | 0,6 Nm            |
| Mounting method                           | inserted, screwed |
| Family construction form                  | M12               |
| Thread                                    | M12 x 1           |
| suitable for corrugated tube (internal Ø) | 10 mm             |
| Cable outlet                              | straight          |
| Coding                                    | A                 |
| Material                                  | PUR               |
| No. of poles                              | 5                 |
| Width across flats                        | SW13              |
| Degree of protection (EN IEC 60529)       | IP65, IP66K, IP67 |
| Side 2                                    |                   |
| Tightening torque                         | 0,6 Nm            |
| Mounting method                           | inserted, screwed |
| Family construction form                  | M12               |
| Thread                                    | M12 x 1           |
| suitable for corrugated tube (internal Ø) | 10 mm             |
| Cable outlet                              | straight          |
| Coding                                    | A                 |
| Material                                  | PUR               |
| No. of poles                              | 5                 |
| Width across flats                        | SW13              |
| Degree of protection (EN IEC 60529)       | IP65, IP66K, IP67 |
| Commercial data                           |                   |
| ECLASS-6.0                                | 27279218          |
| ECLASS-6.1                                | 27279218          |
| ECLASS-7.0                                | 27279218          |
| ECLASS-8.0                                | 27279218          |
| ECLASS-9.0                                | 27060311          |
| ECLASS-10.1                               | 27060311          |

|                       |               |
|-----------------------|---------------|
| ECLASS-11.1           | 27060311      |
| ECLASS-12.0           | 27060311      |
| ETIM-5.0              | EC001855      |
| customs tariff number | 85444290      |
| GTIN                  | 4048879182270 |
| Packaging unit        | 1             |

**Electrical data | Supply**

|                                    |       |
|------------------------------------|-------|
| Operating voltage AC max.          | 125 V |
| Operating voltage DC max.          | 125 V |
| Operating voltage AC (UL-listed)   | 30 V  |
| Operating voltage DC (UL-listed)   | 30 V  |
| Current operating per contact max. | 4 A   |

**Installation | Connection**

|              |         |
|--------------|---------|
| Mounting set | M12 x 1 |
|--------------|---------|

**Device protection | Electrical**

|                                        |                   |
|----------------------------------------|-------------------|
| Degree of protection (EN IEC 60529)    | IP65, IP67, IP66K |
| Additional condition protection degree | inserted, screwed |
| Pollution Degree                       | 3                 |
| Rated surge voltage                    | 1,5 kV            |
| Material group (IEC 60664-1)           | I                 |

**Mechanical data | Material data**

|                           |                  |
|---------------------------|------------------|
| Coating locking           | Nickeled         |
| Coating of fitting        | nickel plated    |
| Locking material          | Zinc die-casting |
| Material screw connection | Zinc die-casting |

**Mechanical data | Mounting data**

|                 |                                       |
|-----------------|---------------------------------------|
| Mounting method | inserted, screwed, Shaking protection |
|-----------------|---------------------------------------|

**Environmental characteristics | Climatic**

|                                        |                            |
|----------------------------------------|----------------------------|
| Operating temperature min.             | -25 °C                     |
| Operating temperature max.             | 85 °C                      |
| Additional condition temperature range | depending on cable quality |

**Important installation notes**

|                        |                                                                                                                                                       |
|------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|
| Note on strain relief  | Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.                                                   |
| Note on bending radius | <b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces. |

**Conformity**

|                  |                          |
|------------------|--------------------------|
| Product standard | DIN EN 61076-2-101 (M12) |
|------------------|--------------------------|

**Cable**

|                                   |                                            |
|-----------------------------------|--------------------------------------------|
| Cable identification              | 225                                        |
| Cable Type                        | 2 (PUR/PVC)                                |
| Approval (cable)                  | UL (AWM-Style 20549/1731), CSA; CE conform |
| Cable weight [g/m]                | 54,78 g                                    |
| Material wire                     | Cu wire, bare                              |
| Resistor (core)                   | max. 57 Ω/km (20 °C)                       |
| Single wire Ø (core)              | 0.1 mm                                     |
| Construction (core)               | 42× 0.1 mm (multi-strand wire class 6)     |
| Diameter (core)                   | 5× 0.34 mm²                                |
| AWG                               | similar to AWG 22                          |
| Material wire isolation           | PVC                                        |
| Material property wire insulation | CFC-, cadmium-, silicone- and lead-free    |
| Shore hardness wire isolation     | 43 ±5 D                                    |

|                                 |                                                                                                                                                        |
|---------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------|
| Wire-Ø incl. isolation          | 1.25 mm ±5%                                                                                                                                            |
| Color/numbering of wires        | br, bk, bl, wh, gnye longitudinally striped                                                                                                            |
| Stranding combination           | 5 wires twisted around central filler                                                                                                                  |
| Shield                          | no                                                                                                                                                     |
| Material jacket                 | PUR/PVC                                                                                                                                                |
| Material property (jacket)      | CFC-, halogen-, cadmium-, silicone- and lead-free, matt, low-adhesion, machine easy to process, abrasion-resistant, hydrolysis and microbial resistant |
| Shore hardness jacket           | 80 ±5 A (PVC-under jacket); 85 ±5 A (PUR-jacket)                                                                                                       |
| Outer-Ø (jacket)                | 5.0 mm ±5%                                                                                                                                             |
| Color jacket                    | gray                                                                                                                                                   |
| chemical resistance             | good resistance to oil, gasoline and chemicals                                                                                                         |
| Nominal voltage                 | UL 300 V AC                                                                                                                                            |
| Test voltage                    | 2000 V AC                                                                                                                                              |
| Current load capacity           | to DIN VDE 0298-4                                                                                                                                      |
| Temperature range (fixed)       | -30...+80 °C                                                                                                                                           |
| Temperature range (mobile)      | -5...+80 °C                                                                                                                                            |
| Bending radius (fixed)          | 10× outer Ø                                                                                                                                            |
| Bending radius (dynamic)        | 15× outer Ø                                                                                                                                            |
| No. of bending cycles (C-track) | max. 2 Mio. (25 °C)                                                                                                                                    |
| Travel speed (C-track)          | max. 3.3 m/s                                                                                                                                           |
| Acceleration (C-track)          | max. 5 m/s <sup>2</sup>                                                                                                                                |