M12 male 0° / M8 female 0° A-cod.

PUR 4x0.25 bk UL/CSA+drag ch. 0.5m

Art.No.: 7000-40581-6310050
Weight: 0.027 kg
Country of origin: DE
Model designation: MSFL0-A-T631_0.5

Male straight - female straight
M12 - M8, 4-pole
Art-No. 7005 - M12/M8 Lite - (plastic hexagonal screw) on request
With cable grommet
Plastic housings with good resistance against chemicals and oils.
The resistance to aggressive media should be individually tested for your application. Further details on request.
Further cable lengths on request.

Link to Product

Illustration









The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-11-18









Product may differ from Image

Cable length	0,50 m
Side 1-1	
Family construction form	M12
No. of poles	4
Coding	A
Gender	Male
Mounting method	Inserted, Screwed
Thread	M12x1
Tightening torque	0.6 Nm
Width across flats	SW 13
Cable outlet	straight
Suitable for corrugated tube (internal Ø)	10 mm
Material	PUR
Material contact	Copper alloy
Coating contact	Gold plated
Degree of protection (EN IEC 60529)	IP67, IP66K, IP65
Side 2-2	

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-11-18

Family construction form	M8
No. of poles	4
Coding	A
Gender	Female
Mounting method	Inserted, Screwed
Thread	M8x1
Tightening torque	0.4 Nm
Width across flats	SW 9
Cable outlet	straight
Suitable for corrugated tube (internal Ø)	6.5 mm
Material	PUR
Material contact	Copper alloy
Coating contact	Gold plated
Degree of protection (EN IEC 60529)	IP67, IP66K, IP65
Commercial data	
URL webshop	https://shop.murrelektronik.com/7000-40581-6310050
GTIN	4048879839938
EU-Customs tariff number	85444290
US-Customs tariff number	8544429090
ECLASS-6.0	27279218
ECLASS-6.1	27279218
ECLASS-7.0	27279218
ECLASS-7.1	27279218
ECLASS-8.0	27279218
ECLASS-8.1	27279218
ECLASS-9.0	27060311
ECLASS-9.1	27060311
ECLASS-10.0.1	27060311
ECLASS-10.1	27060311
ECLASS-11.0	27060311
ECLASS-11.1	27060311
ECLASS-12.0	27060311
ECLASS-13.0	27060311
ECLASS-14.0	27060311
ETIM-5.0	EC001855
ETIM-6.0	EC001855
ETIM-7.0	EC001855
ETIM-8.0	EC001855
ETIM-9.0	EC001855
ETIM-10.0	EC001855
customs tariff number	85444290
EAN	4048879839938
Packaging unit	1
Electrical data | Supply	
Operating voltage AC max.	50 V
Operating voltage DC max.	60 V
Current operating per contact max.	4 A
Operating voltage AC (UL Listed)	30 V
Operating voltage DC (UL Listed)	30 V
Diagnostics	
Status indication LED	No
Device protection | Electrical	

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-11-18

Additional condition degree of protection	Inserted, Screwed
Pollution degree	3
Rated surge voltage	1.5 kV
Insulating material group (IEC 60664-1)	I
Mechanical data | Material data	
Screw connection	Zinc die-casting
Coating of fitting	Nickel plated
Gasket	FKM
Mechanical data | Mounting data	
Mounting method	Inserted, Screwed, Shaking protection
Environmental characteristics | Climatic	
Operating temperature min.	-30 °C
Operating temperature max.	85 °C
Additional condition temperature range	Depending on connected cable
Important installation notes	
Note on bending radius	**Attention:** Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
Conformity	
Product standard	EN IEC 61076-2-101 (M12), EN/IEC 61076-2-104 (M8)
Installation | Cable-1	
Cable identification	631
Cable Type	3
Cable weigth	25.3 g/m
Stranding	1 × 4 wires stranded
Wire arrangement	BN, BK, BU, WH
Material wire insulation	PP
Amount wires	4
Outer diameter wire insulation	1.25 mm ± 0.05 mm
Conductor crosssection (wire)	0.25 mm²
Material conductor wire	Stranded copper wire, bare
Core construction (wire)	32 × 0.1 mm
Ingredient freeness wire insulation	Lead-free, Cadmium-free, CFC-free, Halogen-free, Silicone-free
Material jacket	PUR
Outer-diameter (jacket)	4.5 mm ± 5 %
Jacket color	black / RAL 9005
Freedom from ingredients (jacket)	Lead-free, Cadmium-free, CFC-free, Halogen-free, Silicone-free
Material property (jacket)	Abrasion-resistant, Low adhesion, Good machinability, Matte
Conductor resistance (wire)	79 Ω/km @ 20 °C
Current load capacity (standard)	To DIN VDE 0298-4
Current load capacity max. (wire)	4 A
Nominal voltage max.	300 V
Withstand voltage (wire - wire)	2.5 kV @ 60 s
Withstand voltage (wire - jacket)	2.5 kV @ 60 s
Operating temperature (static)	-40 °C … 80 °C / 90 °C @ 10000 h Operation
Operating temperature (dynamic)	-25 °C … 80 °C / 90 °C @ 10000 h Operation
Operating temperature (drag chain)	-25 °C … 80 °C / 90 °C @ 10000 h Operation
Flame resistance	UL 1581 § 1090, CSA FT2, IEC 60332-2-2
Oil resistance	IEC 60811-404
Chemical resistance	Good
Other resistances	Good resistance to gasoline, Hydrolysis-resistant, Microbe-resistant
Notes	Application-related testing

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-11-18

Bending radius (fixed)	5 × Outer diameter
Bending radius (dynamic)	10 × Outer diameter
No. of bending cycles (C-track)	10 Mio. @ 25 °C
Traversing distance (C-track)	10 m @ 25 °C | horizontal
Travel speed (C-track)	3 m/s @ 25 °C
Acceleration (C-track)	10 m/s² @ 25 °C
No. of torsion cycles	2 Mio.
Torsional stress	± 180 °/m
Torsion speed	35 cycles/min

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-11-18