M12 male 0° / M12 female 0° A-cod. shielded

PUR 8x0.25 shielded bk UL/CSA+drag ch. 15m

Art.No.: 7000-48041-7171500
Weight: 0.922 kg
Country of origin: CZ
Model designation: MSBL0-A-08D717_15.0-ZE

Advantages of our connectors:

Our connectors are versatile and specially optimised for industrial environments. All connectors are 100% tested during the manufacturing process to ensure the highest quality and reliability.

The contacts are gold-plated, which ensures optimum conductivity. Thanks to the high degree of protection, the connectors are ideal for demanding industrial environments. They are also vibration-resistant - this is ensured by the union nut with vibration protection.

Our connectors are resistant to oils and cooling lubricants, but resistance to aggressive media should be tested for each specific application. Different cable lengths available on request

If you are missing technical information? Please feel free to use our dictionary to find more technical details.

Product details:

Male straight - female straight
M12 - M12, 8-pole
Shielded
Plastic housings with good resistance against chemicals and oils.
The resistance to aggressive media should be individually tested for your application. Further details on request.
Further cable lengths on request.

Link to Product

Illustration



The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-11-18











Product may differ from Image

Cable length	15,00 m
Side 1-1	
Family construction form	M12

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-11-18

No. of poles	8
Coding	A
Gender	Male
Mounting method	Inserted, Screwed
Thread	M12x1
Tightening torque	0.6 Nm
Width across flats	SW 13
Cable outlet	straight
Material contact	Copper alloy
Coating contact	Gold plated
Degree of protection (EN IEC 60529)	IP65, IP66K, IP67

Side 2-2

Family construction form	M12
No. of poles	8
Coding	A
Gender	Female
Mounting method	Inserted, Screwed
Thread	M12x1
Tightening torque	0.6 Nm
Width across flats	SW 13
Cable outlet	straight
Material contact	Copper alloy
Coating contact	Gold plated
Degree of protection (EN IEC 60529)	IP65, IP66K, IP67

Commercial data

URL webshop	https://shop.murrelektronik.com/7000-48041-7171500
GTIN	4048879655842
EU-Customs tariff number	85444290
US-Customs tariff number	8544429090
ECLASS-6.0	27279218
ECLASS-6.1	27279218
ECLASS-7.0	27279218
ECLASS-7.1	27279218
ECLASS-8.0	27279218
ECLASS-8.1	27279218
ECLASS-9.0	27060311
ECLASS-9.1	27060311
ECLASS-10.0.1	27060311
ECLASS-10.1	27060311
ECLASS-11.0	27060311
ECLASS-11.1	27060311
ECLASS-12.0	27060311
ECLASS-13.0	27060311
ECLASS-14.0	27060311
ETIM-5.0	EC001855
ETIM-6.0	EC001855
ETIM-7.0	EC001855
ETIM-8.0	EC001855
ETIM-9.0	EC001855
ETIM-10.0	EC001855
customs tariff number	85444290
EAN	4048879655842
Packaging unit	1

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-11-18

Electrical data | Supply	
Operating voltage AC max.	30 V
Operating voltage DC max.	30 V
Current operating per contact max.	2 A
Operating voltage AC (UL Listed)	30 V
Operating voltage DC (UL Listed)	30 V
Installation | Pin assignment	
Assignment	Fully used
Device protection | Electrical	
Degree of protection (EN IEC 60529)	IP67, IP66K, IP65
Additional condition degree of protection	Inserted, Screwed
Pollution degree	3
Rated surge voltage	0.8 kV
Insulating material group (IEC 60664-1)	I
Mechanical data	
Contour for corrugated hose	without
Mechanical data | Material data	
Housing color	black
Color contact carrier	green
Screw connection	Zinc die-casting
Coating of fitting	Nickel plated
Locking material	Zinc die-casting
Coating locking	Matt nickel-plated
Mechanical data | Mounting data	
Mounting method	Inserted, Screwed, Shaking protection
Environmental characteristics | Climatic	
Operating temperature min.	-30 °C
Operating temperature max.	85 °C
Additional condition temperature range	Depending on connected cable
Important installation notes	
Note on bending radius	**Attention:** Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
Conformity	
Product standard	EN IEC 61076-2-101 (M12)
Installation | Cable-1	
Cable identification	717
Cable Type	3
Cable weigth	60 g/m
Stranding	1 × 8 wires around core filler twisted
Cable shielding (type)	Copper braid, tinned
Cable shielding (coverage)	80 %
Banding	Foil, Nonwoven
Filler	Yes
Wire arrangement	BN, WH, RD, BU, PK, GY, YE, GN
Shielding	Shielded
Material wire insulation	PP
Amount wires	8
Outer diameter wire insulation	1.2 mm ± 0.1 mm
Conductor crosssection (wire)	0.25 mm²
Material conductor wire	Stranded copper wire, bare

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-11-18

Core construction (wire)	32 × 0.1 mm
Ingredient freeness wire insulation	Lead-free, Cadmium-free, CFC-free, Halogen-free, Silicone-free
Material jacket	PUR
Outer-diameter (jacket)	7 mm ± 5 %
Jacket color	black / RAL 9005
Freedom from ingredients (jacket)	Lead-free, Cadmium-free, CFC-free, Halogen-free, Silicone-free
Material property (jacket)	Abrasion-resistant, Low adhesion, Good machinability, Matte
Cable shielding (type)	Copper braid, tinned
Cable shielding (coverage)	80 %
Conductor resistance (wire)	79 Ω/km @ 20 °C
Current load capacity (standard)	To DIN VDE 0298-4
Current load capacity max. (wire)	3 A
Nominal voltage max.	300 V
Withstand voltage (wire - wire)	2 kV @ 60 s
Withstand voltage (wire - jacket)	2 kV @ 60 s
Withstand voltage (wire - shield)	2 kV @ 60 s
Operating temperature (static)	-40 °C … 80 °C / 90 °C @ 10000 h Operation
Operating temperature (dynamic)	-25 °C … 80 °C / 90 °C @ 10000 h Operation
Operating temperature (drag chain)	-25 °C … 80 °C / 90 °C @ 10000 h Operation
Flame resistance	UL 1581 § 1090, CSA FT2, IEC 60332-2-2
Oil resistance	IEC 60811-404
Chemical resistance	Good
Other resistances	Good resistance to gasoline, Hydrolysis-resistant, Microbe-resistant
Notes	Application-related testing
Bending radius (fixed)	5 × Outer diameter
Bending radius (dynamic)	10 × Outer diameter
No. of bending cycles (C-track)	5 Mio. @ 25 °C
Traversing distance (C-track)	5 m @ 25 °C | horizontal
Travel speed (C-track)	3.3 m/s @ 25 °C
Acceleration (C-track)	5 m/s² @ 25 °C
No. of torsion cycles	5 Mio.
Torsional stress	± 360 °/m
Torsion speed	35 cycles/min

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-11-18