

**M12 male 0° / M12 female 0° B-cod. shielded**

PUR 1x2xAWG24 shielded vt UL/CSA+drag ch. 1.5m

**PROFIBUS**

Male straight – female straight

M12, 4-pole – M12, 2-pole



B-coded

shielded

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

Further cable lengths on request.

[Link to Product](#)**Illustration**



Product may differ from Image



|                           |                   |
|---------------------------|-------------------|
| Cable length              | 1,5 m             |
| Side 1                    |                   |
| Tightening torque         | 0,6 Nm            |
| Mounting method           | inserted, screwed |
| Family construction form  | M12               |
| Thread                    | M12 x 1           |
| Coding                    | B                 |
| Material                  | PUR               |
| Width across flats        | SW13              |
| Side 2                    |                   |
| Tightening torque         | 0,6 Nm            |
| Mounting method           | inserted, screwed |
| Family construction form  | M12               |
| Thread                    | M12 x 1           |
| Coding                    | B                 |
| Material                  | PUR               |
| Commercial data           |                   |
| ECLASS-6.0                | 27061801          |
| ECLASS-6.1                | 27060307          |
| ECLASS-7.0                | 27060307          |
| ECLASS-8.0                | 27060307          |
| ECLASS-9.0                | 27060307          |
| ECLASS-10.1               | 27060307          |
| ECLASS-11.1               | 27060307          |
| ECLASS-12.0               | 27060307          |
| ETIM-5.0                  | EC001855          |
| customs tariff number     | 85444290          |
| GTIN                      | 4048879142472     |
| Packaging unit            | 1                 |
| Electrical data   Supply  |                   |
| Operating voltage AC max. | 60 V              |
| Operating voltage DC max. | 60 V              |

|                                    |      |
|------------------------------------|------|
| Operating voltage AC (UL-listed)   | 30 V |
| Operating voltage DC (UL-listed)   | 30 V |
| Current operating per contact max. | 4 A  |

#### Device protection | Electrical

|  |                         |
|--|-------------------------|
| Degree of protection (EN IEC 60529)    | IP65, IP67, IP68, IP66K |
| Additional condition protection degree | inserted, screwed       |
| Pollution Degree                       | 3                       |
| Rated surge voltage                    | 1,5 kV                  |
| Material group (IEC 60664-1)           | I                       |

#### Mechanical data

|                             |         |
|-----------------------------|---------|
| Contour for corrugated hose | without |
|-----------------------------|---------|

#### Mechanical data | Material data

|                  |                  |
|------------------|------------------|
| Coating locking  | Nickeled         |
| Locking material | Zinc die-casting |

#### Mechanical data | Mounting data

|                 |                                       |
|-----------------|---------------------------------------|
| Mounting method | inserted, screwed, Shaking protection |
|-----------------|---------------------------------------|

#### Environmental characteristics | Climatic

|  |                            |
|--|----------------------------|
| Operating temperature min.             | -25 °C                     |
| Operating temperature max.             | 85 °C                      |
| Additional condition temperature range | depending on cable quality |

#### Important installation notes

|                        |   |
|------------------------|---|
| Note on strain relief  | Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.   |
| Note on bending radius | <b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces. |

#### Conformity

|                  |                          |
|------------------|--------------------------|
| Product standard | DIN EN 61076-2-101 (M12) |
|------------------|--------------------------|

#### Installation | Cable

|  |  |
|--|--|
| Cable identification                     | 840  |
| Jacket Color                             | violet   |
| Type of Certificate                      | cURus  |
| Amount stranding                         | 1  |
| Stranding                                | 2 wires twisted  |
| Cable shielding (type)                   | copper braid, tinned   |
| Cable shielding (coverage)               | 70 %   |
| Banding                                  | Fleece, Foil   |
| wire arrangement                         | red, green   |
| Cable weight                             | 82,5 g/m   |
| Material jacket                          | TPE-V  |
| Freedom from ingredients (jacket)        | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free |
| Outer-diameter (jacket)                  | 7,8 mm   |
| Tolerance outer diameter (sheath)        | ± 5 %  |
| Material inner jacket                    | TPE-V  |
| Color (inner jacket)                     | white  |
| Amount wires                             | 2  |
| Outer diameter insulation                | 2,55 mm  |
| Outer diameter tolerance core insulation | ± 5 %  |
| Ingredient freeness wire insulation      | lead-free, CFC-free, halogen-free                              |
| Amount strands (wire)                    | 19   |
| Diameter of single wires                 | 24 AWG   |
| Conductor crosssection (wire)            | 24 AWG   |
| Material conductor wire                  | Stranded copper wire, bare                                     |

|   |  |
|---|--|
| Traversing distance (C-track)                           | 5 m @ 25 °C   horizontal                             |
| Current load capacity (standard)                        | to DIN VDE 0298-4                                    |
| Current load capacity min. wire                         | 3 A  |
| Electrical resistance line constant wire                | 78 Ω/km @ 20 °C                                      |
| Nominal voltage power AC max.                           | 250 V  |
| Electrical capacity line constant (wire - wire) (power) | 30000 pF/km  |
| AC withstand voltage power (wire - shield)              | 1 kV @ 60 s  |
| Power frequency withstand voltage power (wire - jacket) | 1 kV @ 60 s  |
| AC withstand voltage power (wire - wire)                | 1 kV @ 60 s  |
| Min. operating temperature (static)                     | -40 °C   |
| Max. operating temperature (fixed)                      | 80 °C  |
| Operating temperature min. (dynamic)                    | -20 °C   |
| Operating temperature max. (dynamic)                    | 70 °C  |
| Flame resistance  | UL 1581 § 1100 FT2   IEC 60332-2-2   UL 1581 § 1090  |
| chemical resistance                                     | Good, application-related testing                    |
| Gasoline resistance                                     | Good, application-related testing                    |
| Oil resistance  | Good, application-related testing   DIN EN 60811-404 |
| No. of bending cycles (C-track)                         | 5 Mio. @ 25 °C                                       |
| Bending radius (fixed)                                  | 10 x Outer diameter                                  |
| Bending radius (dynamic)                                | 12 x Outer diameter                                  |