

**MSUD double valve C-8mm with cable**

PUR 4x0.75 bk 1,5m

Form C (8 mm)

24 V AC  $\pm 20\%$  / DC  $\pm 25\%$ 

Suppressor diode





Connection cable L = 150 mm

without cable sleeves

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

Further cable lengths on request.

[Link to Product](#)**Illustration**

Product may differ from Image



Cable length

1,5 m

**Side 1**

|                          |                   |
|--------------------------|-------------------|
| Tightening torque        | 0,4 Nm            |
| Mounting method          | inserted, screwed |
| Coating contact          | silver-plated     |
| Family construction form | MSUD              |
| Thread                   | M2.5              |
| Material contact         | Copper alloy      |
| Material                 | PBT               |
| No. of poles             | 4                 |

**Side 2**

|                          |        |
|--------------------------|--------|
| Tightening torque        | 0,4 Nm |
| Family construction form | MSUD   |
| Thread                   | M2.5   |
| Material                 | PBT    |
| No. of poles             | 4      |

**Commercial data**

|                       |               |
|-----------------------|---------------|
| ECLASS-6.0            | 27279218      |
| ECLASS-6.1            | 27279218      |
| ECLASS-7.0            | 27279218      |
| ECLASS-8.0            | 27279218      |
| ECLASS-9.0            | 27060312      |
| ECLASS-10.1           | 27060312      |
| ECLASS-11.1           | 27060312      |
| ECLASS-12.0           | 27060312      |
| ETIM-5.0              | EC001855      |
| customs tariff number | 85444290      |
| GTIN                  | 4048879837477 |
| Packaging unit        | 1             |

**Electrical data | Supply**

|                                    |        |
|------------------------------------|--------|
| Operating voltage AC               | 24 V   |
| Operating voltage AC min.          | 19,2 V |
| Operating voltage AC max.          | 28,8 V |
| Operating voltage DC               | 24 V   |
| Operating voltage DC min.          | 18 V   |
| Operating voltage DC max.          | 30 V   |
| Cut-off peak voltage max.          | 55 V   |
| Current operating per contact max. | 4 A    |
| Current consumption max.           | 4 mA   |

**Diagnostics**

|                       |        |
|-----------------------|--------|
| Status indication LED | yellow |
|-----------------------|--------|

**Device protection | Electrical**

|                                        |                   |
|----------------------------------------|-------------------|
| Degree of protection (EN IEC 60529)    | IP67              |
| Additional condition protection degree | inserted, screwed |
| Pollution Degree                       | 3                 |
| Rated surge voltage                    | 0,8 kV            |
| Material group (IEC 60664-1)           | I                 |
| Additional suppressor                  | Suppressor diode  |

**Mechanical data**

|                             |         |
|-----------------------------|---------|
| Contour for corrugated hose | without |
|-----------------------------|---------|

**Mechanical data | Material data**

|                 |       |
|-----------------|-------|
| Color housing   | black |
| Material gasket | PUR   |

| Mechanical data   Mounting data                   |                                                                                                                                                       |
|---------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|
| Mounting method                                   | inserted, screwed                                                                                                                                     |
| Environmental characteristics   Climatic          |                                                                                                                                                       |
| Operating temperature min.                        | -25 °C                                                                                                                                                |
| Operating temperature max.                        | 85 °C                                                                                                                                                 |
| Additional condition temperature range            | depending on cable quality                                                                                                                            |
| Important installation notes                      |                                                                                                                                                       |
| Note on strain relief                             | Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.                                                   |
| Note on bending radius                            | <b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces. |
| Installation   Cable                              |                                                                                                                                                       |
| Cable identification                              | 627                                                                                                                                                   |
| Cable Type                                        | 2                                                                                                                                                     |
| Printing color of wire insulation                 | white (isolation black)                                                                                                                               |
| Jacket Color                                      | black                                                                                                                                                 |
| Type of Certificate                               | cURus                                                                                                                                                 |
| Amount stranding                                  | 1                                                                                                                                                     |
| Stranding                                         | 4 wires twisted                                                                                                                                       |
| wire arrangement                                  | black 1, black 2, black 3, green-yellow                                                                                                               |
| Cable weight                                      | 74,8 g/m                                                                                                                                              |
| Material jacket                                   | PUR                                                                                                                                                   |
| Shore hardness jacket                             | 85 ± 5 Shore A                                                                                                                                        |
| Freedom from ingredients (jacket)                 | lead-free, cadmium-free, CFC-free, silicone-free                                                                                                      |
| Outer-diameter (jacket)                           | 6,5 mm                                                                                                                                                |
| Tolerance outer diameter (sheath)                 | ± 5 %                                                                                                                                                 |
| Material inner jacket                             | PVC                                                                                                                                                   |
| Color (inner jacket)                              | black                                                                                                                                                 |
| Material wire insulation                          | PVC                                                                                                                                                   |
| Amount wires                                      | 4                                                                                                                                                     |
| Outer diameter insulation                         | 1,8 mm                                                                                                                                                |
| Outer diameter tolerance core insulation          | ± 5 %                                                                                                                                                 |
| Shore hardness wire insulation                    | 43 ± 5 Shore D                                                                                                                                        |
| Ingredient freeness wire insulation               | lead-free, cadmium-free, CFC-free, silicone-free                                                                                                      |
| Printing color of wire insulation                 | white (isolation black)                                                                                                                               |
| Amount strands (wire)                             | 42                                                                                                                                                    |
| Diameter of single wires                          | 0,15 mm                                                                                                                                               |
| Conductor crosssection (wire)                     | 0,75 mm²                                                                                                                                              |
| Material conductor wire                           | Stranded copper wire, bare                                                                                                                            |
| Conductor type (wire)                             | strand class 6                                                                                                                                        |
| Traversing distance (C-track)                     | 5 m @ 25 °C   horizontal                                                                                                                              |
| Nominal voltage AC max.                           | 300 V                                                                                                                                                 |
| Current load capacity (standard)                  | to DIN VDE 0298-4                                                                                                                                     |
| Current load capacity min. wire                   | 12 A                                                                                                                                                  |
| Electrical resistance line constant wire          | 26 Ω/km @ 20 °C                                                                                                                                       |
| AC withstand voltage (wire - wire)                | 2 kV @ 60 s                                                                                                                                           |
| Power frequency withstand voltage (wire - jacket) | 2 kV @ 60 s                                                                                                                                           |
| Min. operating temperature (static)               | -30 °C                                                                                                                                                |
| Max. operating temperature (fixed)                | 80 °C                                                                                                                                                 |
| Operating temperature min. (dynamic)              | -5 °C                                                                                                                                                 |
| Operating temperature max. (dynamic)              | 80 °C                                                                                                                                                 |
| UV resistance                                     | DIN EN ISO 4892-2 A                                                                                                                                   |
| Flame resistance                                  | UL 1581 § 1100 FT2   IEC 60332-2-2   UL 1581 § 1090                                                                                                   |

|                          |                                                      |
|--------------------------|------------------------------------------------------|
| chemical resistance      | Good, application-related testing                    |
| Gasoline resistance      | Good, application-related testing                    |
| Oil resistance           | Good, application-related testing   DIN EN 60811-404 |
| Bending radius (fixed)   | 10 x Outer diameter                                  |
| Bending radius (dynamic) | 15 x Outer diameter                                  |
| Travel speed (C-track)   | 2 Mio. @ 25 °C                                       |