

**RJ45 male 0° / RJ45 male 0°, Gigabit**

FRNC/LS0H 4x2xAWG26 shielded gn UL 3m

Ethernet CAT6A

Male straight – male straight


RJ45 – RJ45, 8-pole  
shielded

without cable sleeves

Further cable lengths on request.

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)**Illustration**

Product may differ from Image

**Approvals**

\* only for products with UL/CSA approved cable

**Form**

Form 74711

**Technical Data**

Operating voltage	max. 60 V DC
Operating voltage (only UL listed)	25 V DC
Rated surge voltage	1.0 kV
Operating current per contact	max. 1.76 A (UL: 1.0 A)
Material group	IEC 60664-1, category I
Transfer parameters	CAT6A
LED display	no
Locking of ports	Snap-in connector
Protection	IP20
Locking material	PA

The information in this brochure has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 07/21

Material	PUR
suitable for corrugated tube (internal Ø)	without

**General data**


Mounting method	inserted
Pollution Degree	3
Temperature range	-25...+85 °C, depending on cable quality

**Cables**

Cable number	478
No./diameter of wires	4x 2x AWG26
Wire isolation	FRNC (wh, bl, wh, or, wh, gn, wh, br)
Jacket Color	green
Material (jacket)	FRNC
Outer Ø	6.0 mm ±5%
Bend radius (moving)	5x outer Ø
Temperature range (fixed)	-20...+60 °C
Temperature range (mobile)	0...+50 °C
Material (wire)	Cu wire, bare
Shield	yes
Color (jacket)	green

**Commercial data**

country of origin	HU
customs tariff number	85444210
EAN	4048879595278
eClass	27061801
Packaging unit	1

**Sketch**

Product may differ from Image