RJ45 male 0° / RJ45 male 0° shielded

FRNC/LS0H 4x2xAWG26 shielded gn UL 2m

Art.No.: 7000-74712-4780200
Weight: 0.118 kg
Country of origin: HU
Model designation: MSRAL0-RA-8p8c4780200

Ethernet Cat6A
Male straight - male straight
RJ45 - RJ45, 8-pole
Shielded
With cable grommet
Further cable lengths on request.
Plastic housings with good resistance against chemicals and oils.
The resistance to aggressive media should be individually tested for your application. Further details on request.

Link to Product

Illustration









The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-11-18







Product may differ from Image

Cable length	2,00 m
Side 1-1	
Family construction form	RJ45
No. of poles	8
Gender	Male
Mounting method	Inserted
Cable outlet	straight
Degree of protection (EN IEC 60529)	IP20
Side 2-2	
Family construction form	RJ45
No. of poles	8
Gender	Male
Mounting method	Inserted
Cable outlet	straight
Degree of protection (EN IEC 60529)	IP20
Commercial data	
URL webshop	https://shop.murrelektronik.com/7000-74712-4780200

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-11-18

GTIN	4048879595506
EU-Customs tariff number	85444210
US-Customs tariff number	8544422000
ECLASS-6.0	27061801
ECLASS-6.1	27060307
ECLASS-7.0	27060307
ECLASS-7.1	27060307
ECLASS-8.0	27060307
ECLASS-8.1	27060307
ECLASS-9.0	27060307
ECLASS-9.1	27060307
ECLASS-10.0.1	27060307
ECLASS-10.1	27060307
ECLASS-11.0	27060307
ECLASS-11.1	27060307
ECLASS-12.0	27060307
ECLASS-13.0	27060307
ECLASS-14.0	27060307
ETIM-5.0	EC002599
ETIM-6.0	EC002599
ETIM-7.0	EC002599
ETIM-8.0	EC002599
ETIM-9.0	EC002599
ETIM-10.0	EC002599
customs tariff number	85444210
EAN	4048879595506
Packaging unit	1
Electrical data | Supply	
Operating voltage DC max.	60 V
Current operating per contact max.	1.5 A
Operating voltage DC max. (UL Listed)	25 V
Industrial Communication	
Transmission rate max.	10 Gbit/s
Transfer parameters	Cat6A
Diagnostics	
Status indication LED	No
Device protection | Electrical	
Degree of protection (EN IEC 60529)	IP20
Additional condition degree of protection	Inserted
Pollution degree	3
Rated surge voltage	1 kV
Insulating material group (IEC 60664-1)	I
Mechanical data	
Contour for corrugated hose	without
Mechanical data | Material data	
Housing	PUR
Locking material	PA
Mechanical data | Mounting data	
Locking techniques	Snap-in connector
Environmental characteristics | Climatic	

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-11-18

Operating temperature min.	-25 °C
Operating temperature max.	85 °C
Additional condition temperature range	Depending on connected cable
Important installation notes	
Note on bending radius	**Attention:** Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
Installation | Cable-1	
Cable identification	478
Cable weigth	43 g/m
Stranding	4 × 2 wires stranded
Stranding (type 2)	1 × 4 stranding combinations stranded
Cable shielding (type)	Copper braid, tinned
Pair shielding (type)	Metal foil
Banding	Foil
Wire arrangement	(WH, BN), (WH, BU), (WH, OG), (WH, GN)
Shielding	Shielded
Cable type	Industrial Ethernet Cat7
Material wire insulation	Cell polyethylene
Amount wires	8
Outer diameter wire insulation	1 mm ± 0.05 mm
Conductor crosssection (wire)	26 AWG
Material conductor wire	Stranded copper wire, bare
Core construction (wire)	7 x 32 AWG
Ingredient freeness wire insulation	Lead-free, CFC-free, Halogen-free
Material jacket	FRNC
Outer-diameter (jacket)	6 mm ± 5 %
Jacket color	green / RAL 6018
Freedom from ingredients (jacket)	Lead-free, CFC-free, Halogen-free
Cable shielding (type)	Copper braid, tinned
Pair shielding (type)	Metal foil
Current load capacity (standard)	To DIN VDE 0298-4
Current load capacity max. (wire)	2 A
Nominal voltage max.	125 V
Withstand voltage (wire - wire)	2.5 kV @ 2 s
Withstand voltage (wire - jacket)	2.5 kV @ 2 s
Withstand voltage (wire - shield)	2.5 kV @ 2 s
Electric capacitance	44000 pF/km
Insulation resistance	5 GΩ × km
Characteristic impedance	100 Ω ± 5 % @ 100 MHz
Operating temperature (static)	-20 °C … 60 °C
Operating temperature (dynamic)	-20 °C … 60 °C
Flame resistance	IEC 60332-1-2, IEC 60332-2-2, IEC 60332-3-24, UL 2556 § 9.4 (VW-1)
Chemical resistance	IEC 60754-2
Other resistances	smoke-tight (IEC 61034-1, IEC 61034-2)
Notes	Application-related testing
Bending radius (dynamic)	4 × Outer diameter

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-11-18