

Adapter M12 male/ female B-cod. / D-Sub 9-pol. 90°

Shielded, 12Mbit/s


PROFIBUS
Bus connection plug 90°
SUB-D9 (male); M12× 1 mm, B-coded
Programming device

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27061801
ECLASS-7.0	27061801
ECLASS-8.0	27061801
ECLASS-9.0	27061801
ECLASS-10.1	27242692
ECLASS-11.1	27242692
ECLASS-12.0	27242692
ETIM-5.0	EC001855
customs tariff number	85366990
GTIN	4048879600392
Packaging unit	1
Electrical data	
Terminating resistor	connectable, integrated
Industrial communication	
Data transmission rate max.	12 MBit/s
Installation Connection	
Family construction form	M12
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP30
Mechanical data Mounting data	
Height	66 mm
Width	62 mm
Depth	17 mm
Environmental characteristics Climatic	

Operating temperature min.	-20 °C
Operating temperature max.	70 °C

Important installation notes

Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.