

**M12 male 0° A-cod. with cable V4A**

PVC 3x0.34 gy UL/CSA 1.5m

Male straight

M12, 3-pole



Art-No. 7005 - M12 Lite - (plastic hexagonal screw) on request

Stainless steel 1.4404 (V4A)


Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

Further cable lengths on request.

[Link to Product](#)**Illustration**

Product may differ from Image



Cable length

1,5 m

**Side 1**

Tightening torque

0,6 Nm

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-06-01

Murrelektronik GmbH | Falkenstraße 3 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

|                                                 |                                                                                                                                                       |
|-------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|
| Family construction form                        | M12                                                                                                                                                   |
| Thread                                          | M12 x 1                                                                                                                                               |
| suitable for corrugated tube (internal Ø)       | 10 mm                                                                                                                                                 |
| Coding                                          | A                                                                                                                                                     |
| Width across flats                              | SW13                                                                                                                                                  |
| Degree of protection (EN IEC 60529)             | IP66K, IP67                                                                                                                                           |
| <b>Commercial data</b>                          |                                                                                                                                                       |
| ECLASS-6.0                                      | 27279218                                                                                                                                              |
| ECLASS-6.1                                      | 27279218                                                                                                                                              |
| ECLASS-7.0                                      | 27279218                                                                                                                                              |
| ECLASS-8.0                                      | 27279218                                                                                                                                              |
| ECLASS-9.0                                      | 27060311                                                                                                                                              |
| ECLASS-10.1                                     | 27060311                                                                                                                                              |
| ECLASS-11.1                                     | 27060311                                                                                                                                              |
| ECLASS-12.0                                     | 27060311                                                                                                                                              |
| ETIM-5.0                                        | EC001855                                                                                                                                              |
| customs tariff number                           | 85444290                                                                                                                                              |
| GTIN                                            | 4048879776080                                                                                                                                         |
| Packaging unit                                  | 1                                                                                                                                                     |
| <b>Electrical data   Supply</b>                 |                                                                                                                                                       |
| Operating voltage AC max.                       | 250 V                                                                                                                                                 |
| Operating voltage DC max.                       | 250 V                                                                                                                                                 |
| Operating voltage AC (UL-listed)                | 30 V                                                                                                                                                  |
| Operating voltage DC (UL-listed)                | 30 V                                                                                                                                                  |
| Current operating per contact max.              | 4 A                                                                                                                                                   |
| <b>Device protection   Electrical</b>           |                                                                                                                                                       |
| Additional condition protection degree          | inserted, screwed                                                                                                                                     |
| Pollution Degree                                | 3                                                                                                                                                     |
| Material group (IEC 60664-1)                    | I                                                                                                                                                     |
| <b>Mechanical data   Material data</b>          |                                                                                                                                                       |
| Material housing                                | PUR                                                                                                                                                   |
| Locking material                                | Stainless steel 1.4404 (V4A)                                                                                                                          |
| <b>Mechanical data   Mounting data</b>          |                                                                                                                                                       |
| Mounting method                                 | inserted, screwed, Shaking protection                                                                                                                 |
| <b>Environmental characteristics   Climatic</b> |                                                                                                                                                       |
| Operating temperature min.                      | -25 °C                                                                                                                                                |
| Operating temperature max.                      | 85 °C                                                                                                                                                 |
| Additional condition temperature range          | depending on cable quality                                                                                                                            |
| <b>Important installation notes</b>             |                                                                                                                                                       |
| Note on strain relief                           | Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.                                                   |
| Note on bending radius                          | <b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces. |
| <b>Conformity</b>                               |                                                                                                                                                       |
| Product standard                                | DIN EN 61076-2-101 (M12)                                                                                                                              |
| <b>Installation   Cable</b>                     |                                                                                                                                                       |
| wire arrangement                                | brown, black, blue                                                                                                                                    |
| Cable identification                            | 213                                                                                                                                                   |
| Cable Type                                      | 1                                                                                                                                                     |
| Jacket Color                                    | gray                                                                                                                                                  |
| Type of Certificate                             | cURus                                                                                                                                                 |
| Amount stranding                                | 1                                                                                                                                                     |

|                                                   |                                                      |
|---------------------------------------------------|------------------------------------------------------|
| Stranding                                         | 3 wires twisted                                      |
| wire arrangement                                  | brown, black, blue                                   |
| Cable weight                                      | 34,1 g/m                                             |
| Material jacket                                   | PVC                                                  |
| Shore hardness jacket                             | 85 ± 5 Shore A                                       |
| Freedom from ingredients (jacket)                 | lead-free, cadmium-free, CFC-free, silicone-free     |
| Outer-diameter (jacket)                           | 4,6 mm                                               |
| Tolerance outer diameter (sheath)                 | ± 5 %                                                |
| Material wire insulation                          | PVC                                                  |
| Amount wires                                      | 3                                                    |
| Outer diameter insulation                         | 1,25 mm                                              |
| Outer diameter tolerance core insulation          | ± 5 %                                                |
| Shore hardness wire insulation                    | 45 ± 5 Shore D                                       |
| Material properties wire insulation               | good machinability                                   |
| Ingredient freeness wire insulation               | lead-free, cadmium-free, CFC-free, silicone-free     |
| Amount strands (wire)                             | 19                                                   |
| Diameter of single wires                          | 0,15 mm                                              |
| Conductor crosssection (wire)                     | 0,34 mm²                                             |
| Material conductor wire                           | Stranded copper wire, bare                           |
| Conductor type (wire)                             | Strand class 5                                       |
| Nominal voltage AC max.                           | 300 V                                                |
| Current load capacity (standard)                  | to DIN VDE 0298-4                                    |
| Current load capacity min. wire                   | 6 A                                                  |
| Electrical resistance line constant wire          | 57 Ω/km @ 20 °C                                      |
| AC withstand voltage (wire - wire)                | 2 kV @ 60 s                                          |
| Power frequency withstand voltage (wire - jacket) | 2 kV @ 60 s                                          |
| Min. operating temperature (static)               | -30 °C                                               |
| Max. operating temperature (fixed)                | 80 °C                                                |
| Operating temperature min. (dynamic)              | -5 °C                                                |
| Operating temperature max. (dynamic)              | 80 °C                                                |
| Flame resistance                                  | IEC 60332-2-2   UL 1581 § 1100 FT2   UL 1581 § 1090  |
| chemical resistance                               | Good, application-related testing                    |
| Gasoline resistance                               | Good, application-related testing                    |
| Oil resistance                                    | Good, application-related testing   DIN EN 60811-404 |
| Bending radius (fixed)                            | 5 x Outer diameter                                   |
| Bending radius (dynamic)                          | 10 x Outer diameter                                  |