

MVP-METALL, 4XM12, 5POLE, PRE-WIRED CABLE

10.0m PUR 8x0,34+3X0.75, UL/CSA

4-way, 5-pole  
10.0 m  
shielded  
Replaces identical product (Art.No. 27488)  
without LED, 5-pole (for analog signals)  
Further cable lengths on request.

Link to Product

Illustration



Product may differ from Image



Commercial data

|            |          |
|------------|----------|
| ECLASS-6.0 | 27279219 |
| ECLASS-6.1 | 27279219 |
| ECLASS-7.0 | 27279219 |
| ECLASS-8.0 | 27279219 |

|                       |               |
|-----------------------|---------------|
| ECLASS-9.0            | 27440108      |
| ECLASS-10.1           | 27440108      |
| ECLASS-11.1           | 27440108      |
| ECLASS-12.0           | 27440108      |
| ETIM-5.0              | EC002585      |
| customs tariff number | 85444290      |
| GTIN                  | 4048879351737 |
| Packaging unit        | 1             |

**Electrical data | Supply**

|                                    |      |
|------------------------------------|------|
| Operating voltage AC max.          | 48 V |
| Operating voltage DC max.          | 48 V |
| Current operating per contact max. | 4 A  |

**Installation | Connection**

|              |         |
|--------------|---------|
| Mounting set | M12 x 1 |
|--------------|---------|

**Device protection | Electrical**

|                                     |                  |
|-------------------------------------|------------------|
| Degree of protection (EN IEC 60529) | IP65, IP67, IP68 |
|-------------------------------------|------------------|

**Mechanical data | Material data**

|                  |                  |
|------------------|------------------|
| Coating housing  | Nickel           |
| Material housing | Zinc die-casting |

**Mechanical data | Mounting data**

|                 |                |
|-----------------|----------------|
| Mounting method | Schraubgewinde |
|-----------------|----------------|

**Environmental characteristics | Climatic**

|  |                            |
|--|----------------------------|
| Operating temperature min.             | -25 °C                     |
| Operating temperature max.             | 90 °C                      |
| Additional condition temperature range | depending on cable quality |

**Installation | Cable**

|                                   |  |
|-----------------------------------|--|
| Cable identification              | 373  |
| Jacket Color                      | gray   |
| Type of Certificate               | cURus  |
| Amount stranding                  | 1  |
| Stranding                         | 3 wires twisted  |
| Stranding factor min.             | 43 mm  |
| Stranding factor max.             | 43 mm  |
| Amount stranding (type 2)         | 1  |
| Stranding (type 2)                | 8 wires around Stranding combination counter-rotating twisted  |
| Stranding factor min. (type 2)    | 90 mm  |
| Stranding factor max. (type 2)    | 90 mm  |
| Cable shielding (type)            | copper braid, tinned   |
| Cable shielding (coverage)        | 80 %   |
| Banding                           | Fleece, Foil   |
| wire arrangement                  | yellow, white, green, (blue, brown, green-yellow, gray, gray-pink, red-blue, green-white, brown-green) |
| No. of bending cycles (C-track)   | 5 Mio.   |
| Cable weight                      | 145,2 g/m  |
| Material jacket                   | PUR  |
| Shore hardness jacket             | 85 Shore A   |
| Freedom from ingredients (jacket) | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free, LABS-free                              |
| Outer-diameter (jacket)           | 9,3 mm   |
| Tolerance outer diameter (sheath) | ± 5 %  |
| Material wire insulation          | TPE-E  |
| Amount wires                      | 8  |
| Outer diameter insulation         | 1,4 mm   |

|   |   |
|---|---|
| Outer diameter tolerance core insulation                | ± 5 %   |
| Shore hardness wire insulation                          | 55 Shore D  |
| Ingredient freeness wire insulation                     | lead-free, CFC-free, halogen-free, silicone-free, LABS-free |
| Amount strands (wire)                                   | 42  |
| Diameter of single wires                                | 0,1 mm  |
| Conductor crosssection (wire)                           | 0,34 mm²  |
| Material conductor wire                                 | Stranded copper wire, bare                                  |
| Conductor type (wire)                                   | strand class 6  |
| Material wire insulation (Data)                         | TPE-E   |
| Outer diameter wire insulation (Data)                   | 1,8 mm  |
| Tolerance outer diameter wire insulation (data)         | ± 5 %   |
| Shore hardness wire insulation (Data)                   | 55 Shore D  |
| Ingredient freeness wire insulation (Data)              | lead-free, CFC-free, halogen-free, silicone-free, LABS-free |
| Amount wires (Data)                                     | 3   |
| Amount strands wire (Data)                              | 96  |
| Diameter of single wires (Data)                         | 0,1 mm  |
| Conductor crosssection wire (Data)                      | 0,75 mm²  |
| Material conductor wire (Data)                          | Stranded copper wire, bare                                  |
| Wire conductor type (Data)                              | strand class 6  |
| Current load capacity (standard)                        | to DIN VDE 0298-4   |
| Current load capacity min. wire                         | 4 A   |
| Current load capacity min. Wire (Data)                  | 12 A  |
| Electrical resistance line constant wire                | 53 Ω/km @ 20 °C   |
| Electrical resistance coating wire (Data)               | 26 Ω/km @ 20 °C   |
| Max. rated voltage power (conductor - ground)           | 300 V   |
| Max. rated voltage power (conductor - conductor)        | 500 V   |
| AC withstand voltage power (wire - shield)              | 2 kV @ 60 s   |
| Power frequency withstand voltage power (wire - jacket) | 2 kV @ 60 s   |
| AC withstand voltage power (wire - wire)                | 2 kV @ 60 s   |
| Min. operating temperature (static)                     | -40 °C  |
| Max. operating temperature (fixed)                      | 90 °C   |
| Operating temperature min. (dynamic)                    | -40 °C  |
| Operating temperature max. (dynamic)                    | 90 °C   |
| Flame resistance  | UL 1581 § 1090   IEC 60332-2-2   UL 1581 § 1100 FT2         |
| chemical resistance                                     | Good, application-related testing                           |
| Gasoline resistance                                     | Good, application-related testing                           |
| Oil resistance  | Good, application-related testing   DIN EN 60811-404        |
| Bending radius (installation)                           | x Outer diameter  |
| Bending radius (fixed)                                  | x Outer diameter  |
| Bending radius (dynamic)                                | 12 x Outer diameter   |

#### Connection type 2

|                          |                |
|--------------------------|----------------|
| Family construction form | free cable end |
| No. of poles             | 16             |
| Family construction form | M12            |
| Gender                   | female         |
| Color contact carrier    | black          |
| Coding                   | A              |
| No. of poles             | 5              |
| PIN 1                    | +              |
| PIN 2                    | NC S 2         |
| PIN 3                    | -              |
| PIN 4                    | NO S 1         |

PIN 5

PE