


**EXACT8, 10XM8, 4 POLE MOULDED CABLE**

5.0m PUR 20\*0,34+2\*0,75 exit norm..



5.0 m

[Link to Product](#)

**Illustration**




**M8-Females 4-pole**



Product may differ from Image

**Approvals**



### More Info

Bus technologies

### Form

Form 80110

### Technical Data

Operating voltage	24 V DC
Operating current per contact	max. 2 A
Locking of ports	Screw thread (M8×1 mm)
Protection	IP65/IP67
Housing	Plastic, flame retardant
Signal per port	2
Total current	max. 8 A

### General data

Temperature range -20...+80 °C, depending on cable quality

### Cables

No./diameter of wires	20× 0.34 + 2× 0.75 mm <sup>2</sup>
C-track properties	5 Mio.
Outer Ø	11.3 mm ±5%
Cable number	411
Approval (cable)	UL (AWM-Style 20233), CSA
Jacket Color	gray
Temperature range (fixed)	-40...+80 °C
Temperature range (mobile)	-5...+60 °C
Bend radius (fixed)	5× outer Ø
Bend radius (moving)	10× outer Ø
Material (jacket)	PUR (UL/CSA)

### Contact Layout

PIN 1	(+)
PIN 2	(NC)/(S2)
PIN 3	(-)
PIN 4	(NO)/(S1)

LED (green): Power / LED (yellow): (S1) / LED (white): Signal (S2)

### Commercial data

country of origin	DE
customs tariff number	85444290
EAN	4048879056717
eClass	27279219
Packaging unit	1.000