



AMMDS 10-44/1 OPTO-COUPLER MODULE

IN: 35 VDC - OUT: 35 VDC / 0.2 A


Transistor 0.2 A
24 V DC
with minus plug link
Double terminals on the output side
for rapid switching

Link do produto

Ilustração



Produto pode diferir da imagem



General product information

Scope of delivery Jumper (Art-No. 90960)

Dados comerciais

ECLASS-6.0	27371604
ECLASS-6.1	27371604
ECLASS-7.0	27371604

ECLASS-8.0	27371604
ECLASS-9.0	27371604
ECLASS-10.1	27371604
ECLASS-11.1	27371604
ECLASS-12.0	27371604
ETIM-5.0	EC001504
Classificação fiscal	85414900
GTIN	4048879027977
Quantidade por embalagem	1
Electrical data Input	
Input voltage OFF DC min.	0 V
Input voltage OFF DC max.	5 V
Input voltage DC min.	10 V
Input voltage DC max.	35 V
Input current	10 mA
Electrical data Output	
Switch off delay max.	14 µs
Quiescent current OFF max.	0,3 mA
Switching frequency inductive max.	200 Hz
Switching frequency ohmic max.	20000 Hz
Voltage switching DC min.	5 V
Switching voltage DC max.	35 V
Switching current min.	1 mA
Switching current max.	0,2 A
Voltage drop DC max.	0,5 V
Diagnostics	
Status indication LED	red
Device protection Electrical	
Rated surge voltage	2,5 kV
Device protection Media	
Flame resistance	flame retardant
Mechanical data Material data	
Color housing	black
Material housing	Plastic
Mechanical data Mounting data	
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, G32, (EN 60715)
Height	68 mm
Width	82 mm
Depth	12 mm
Environmental characteristics Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	60 °C
Connection type 3	
Connection type 1	Input
Connection type 2	Output
Connection type 3	Output
Connection	Screw terminals SK
Family construction form	terminal
Gender	female

No. of poles	2
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
No. of poles	2
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
No. of poles	2
PIN 1	+ 14
PIN 2	13