


MA5I67 I/O MODULE

4 digital inputs

Digital inputs  
DI4 - 0.2 A (AB) - 4× M12  
Y-wiring  
Connection cables are in the online shop under "Connection Technology".  
Housing fully potted.

Link do produto

Ilustração



Produto pode diferir da imagem



| Dados comerciais                   |               |
|------------------------------------|---------------|
| ECLASS-6.0                         | 27242604      |
| ECLASS-6.1                         | 27242604      |
| ECLASS-7.0                         | 27242604      |
| ECLASS-8.0                         | 27242604      |
| ECLASS-9.0                         | 27242604      |
| ECLASS-10.1                        | 27242604      |
| ECLASS-11.1                        | 27242604      |
| ECLASS-12.0                        | 27242604      |
| ETIM-5.0                           | EC001599      |
| Classificação fiscal               | 85176200      |
| GTIN                               | 4048879049009 |
| Quantidade por embalagem           | 1             |
| Electrical data                    |               |
| Y-wiring                           | yes           |
| Electrical data   Supply           |               |
| Bus voltage AS-Interface DC min.   | 26,5 V        |
| Bus voltage AS-Interface DC max.   | 31,6 V        |
| Current consumption AS-i port max. | 250 mA        |
| Electrical data   Input            |               |

|                                                 |                                                |
|-------------------------------------------------|------------------------------------------------|
| Overload resistant                              | yes                                            |
| Short-circuit protected                         | yes                                            |
| Type input                                      | PNP, for 3-wire sensors or mechanical switches |
| Current carrying capacity max.                  | 0,17 A                                         |
| <b>Industrial communication   Bus data</b>      |                                                |
| Address setting type                            | Addressing socket, Master                      |
| Slave address range                             | (0), 1 A...31 A, 1 B...31 B                    |
| <b>Industrial communication   AS-Interface</b>  |                                                |
| Profile (IO.ID.ID2)                             | S-0.A.2                                        |
| <b>Diagnostics</b>                              |                                                |
| Diagnostic via BUS                              | yes                                            |
| Diagnostic via LED                              | per module                                     |
| LED display                                     | Ethernet connection/data traffic               |
| <b>Device protection   Electrical</b>           |                                                |
| Degree of protection (EN IEC 60529)             | IP67                                           |
| <b>Mechanical data   Mounting data</b>          |                                                |
| Mounting method                                 | screwed, geschnappt                            |
| Suitable for mounting type                      | mounting rail, (EN 60715)                      |
| Height                                          | 94 mm                                          |
| Width                                           | 60 mm                                          |
| Depth                                           | 39 mm                                          |
| <b>Environmental characteristics   Climatic</b> |                                                |
| Operating temperature min.                      | -20 °C                                         |
| Operating temperature max.                      | 60 °C                                          |
| Storage temperature min.                        | -20 °C                                         |
| Storage temperature max.                        | 70 °C                                          |
| <b>Connection type 2</b>                        |                                                |
| Connection type 1                               | 2                                              |
| Connection type 2                               | 3                                              |
| Family construction form                        | M12                                            |
| Gender                                          | female                                         |
| Color contact carrier                           | black                                          |
| Coding                                          | A                                              |
| No. of poles                                    | 5                                              |
| PIN 1                                           | Usens +                                        |
| PIN 2                                           | DI                                             |
| PIN 3                                           | Usens -                                        |
| PIN 4                                           | DI                                             |
| PIN 5                                           | n.c.                                           |
| Family construction form                        | M12                                            |
| Gender                                          | female                                         |
| Color contact carrier                           | black                                          |
| Coding                                          | A                                              |
| No. of poles                                    | 5                                              |
| PIN 1                                           | Usens +                                        |
| PIN 2                                           | n.c.                                           |
| PIN 3                                           | Usens -                                        |
| PIN 4                                           | DI                                             |
| PIN 5                                           | n.c.                                           |