


Gateway EtherCAT/AS-i, 2 Masters

Product discontinued since 2023-02-13

Gateway-Singlemaster
via pluggable spring clamp plug-in terminals on the front 0.5...1.5 mm²
AS-Interface/PROFIBUS DP
Specification 3.0
Current manuals, GSD/type data can be downloaded at: www.murrelektronik.com
Other gateways on request.

Link do produto

Ilustração



Produto pode diferir da imagem



Dados comerciais	
ECLASS-6.0	27242608
ECLASS-6.1	27242608
ECLASS-7.0	27242608
ECLASS-8.0	27242608
ECLASS-9.0	27242608
ECLASS-10.1	27242608
ECLASS-11.1	27242608
ECLASS-12.0	27242608
ETIM-5.0	EC001604
Classificação fiscal	85176200
GTIN	4048879444712
Quantidade por embalagem	1
Electrical data	
Rated operating current AS-Interface max.	70 mA
Electrical data Supply	
Operating voltage DC	30 V
Industrial communication Bus data	
Automatic baudrate detection	yes

Baud rate min.	9,6 kBaud
----------------	-----------

Baud rate max.	12 MBaud
----------------	----------

Industrial communication | AS-Interface

AS-i specification	V3.0
--------------------	------

Number of slaves max.	62
-----------------------	----

Diagnostic interface serial	PS2/RS232
-----------------------------	-----------

Cycle time AS-i	150 µs × (number of slaves + 2)
-----------------	---------------------------------

Industrial communication | Profibus

PROFIBUS function	Illustration of AS-Interface slaves as I/O process data in PROFIBUS DP, full diagnostic configuration via DP-master
-------------------	---

Installation | Connection

Family construction form	SUB-D9
--------------------------	--------

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP20
-------------------------------------	------

Overload resistant	yes
--------------------	-----

Short-circuit protected	yes
-------------------------	-----

Rated insulation voltage	500 V
--------------------------	-------

Mechanical data

Number of operating buttons	4
-----------------------------	---

Function operating buttons	ESC, Mode, OK, Set
----------------------------	--------------------

Mechanical data | Mounting data

Mounting method	geschnappt
-----------------	------------

Suitable for mounting type	mounting rail, (EN 60715)
----------------------------	---------------------------

Height	120 mm
--------	--------

Width	75 mm
-------	-------

Depth	70 mm
-------	-------

Environmental characteristics | Climatic

Operating temperature min.	0 °C
----------------------------	------

Operating temperature max.	55 °C
----------------------------	-------

Storage temperature min.	-20 °C
--------------------------	--------

Storage temperature max.	85 °C
--------------------------	-------

Conformities, approvals

Low Voltage Directive	EN 50295
-----------------------	----------