

CUBE67 BUS NODES

CANopen

CANopen  
Connection cables are in the online shop under "Connection Technology".  
Housing fully potted.

Link do produto

Ilustração



Produto pode diferir da imagem



| Dados comerciais                    |               |
|-------------------------------------|---------------|
| ECLASS-6.0                          | 27242608      |
| ECLASS-6.1                          | 27242608      |
| ECLASS-7.0                          | 27242608      |
| ECLASS-8.0                          | 27242608      |
| ECLASS-9.0                          | 27242608      |
| ECLASS-10.1                         | 27242608      |
| ECLASS-11.1                         | 27242608      |
| ECLASS-12.0                         | 27242608      |
| ETIM-5.0                            | EC001604      |
| Classificação fiscal                | 85389099      |
| GTIN                                | 4048879048712 |
| Quantidade por embalagem            | 1             |
| Electrical data   Supply            |               |
| Operating voltage DC                | 24 V          |
| Current consumption max.            | 70 mA         |
| Total current UA max.               | 9 A           |
| Total current US max.               | 9 A           |
| Industrial communication   Bus data |               |
| Address range min.                  | 1             |
| Address range max.                  | 99            |
| Industrial communication   CANopen  |               |

CANopen addressing

Rotary switch

**Diagnostics**

|                         |                                  |
|-------------------------|----------------------------------|
| Diagnostic              | No voltage, Under voltage        |
| Diagnostic via BUS      | per module and channel           |
| Diagnostic via LED      | per module and channel           |
| Short circuit diagnosis | yes                              |
| LED display             | Ethernet connection/data traffic |
| Overload diagnosis      | yes                              |

**Device protection | Electrical**

|                                     |      |
|-------------------------------------|------|
| Degree of protection (EN IEC 60529) | IP67 |
|-------------------------------------|------|

**Mechanical data**

|                               |    |
|-------------------------------|----|
| Number extension modules max. | 16 |
|-------------------------------|----|

**Mechanical data | Mounting data**

|                            |                       |
|----------------------------|-----------------------|
| Suitable for mounting type | 2-hole screw mounting |
| Height                     | 151 mm                |
| Width                      | 50 mm                 |
| Depth                      | 50,3 mm               |

**Environmental characteristics | Climatic**

|                            |        |
|----------------------------|--------|
| Operating temperature min. | 0 °C   |
| Operating temperature max. | 55 °C  |
| Storage temperature min.   | -20 °C |
| Storage temperature max.   | 75 °C  |

**Conformity**

|                  |            |
|------------------|------------|
| Product standard | EN 61131-2 |
|------------------|------------|

**Connection type 4**

|                          |                            |
|--------------------------|----------------------------|
| Connection type 1        | Bus In                     |
| Connection type 2        | Bus Out                    |
| Connection type 3        | Internal system connection |
| Connection type 4        | Power                      |
| Family construction form | M12                        |
| Gender                   | male                       |
| Color contact carrier    | black                      |
| Coding                   | A                          |
| No. of poles             | 5                          |
| PIN 1                    | Shield                     |
| PIN 2                    | n.c.                       |
| PIN 3                    | 0 V                        |
| PIN 4                    | CAN_HIGH                   |
| PIN 5                    | CAN_LOW                    |
| Family construction form | M12                        |
| Gender                   | female                     |
| Color contact carrier    | black                      |
| Coding                   | A                          |
| No. of poles             | 5                          |
| PIN 1                    | Shield                     |
| PIN 2                    | n.c.                       |
| PIN 3                    | 0 V                        |
| PIN 4                    | CAN_HIGH                   |
| PIN 5                    | CAN_LOW                    |
| Family construction form | M12                        |
| Gender                   | female                     |

|                          |              |
|--------------------------|--------------|
| Color contact carrier    | black        |
| Coding                   | A            |
| No. of poles             | 6            |
| PIN 1                    | 24 V DC (UA) |
| PIN 2                    | 24 V DC (US) |
| PIN 3                    | 0 V          |
| PIN 4                    | Bus internal |
| PIN 5                    | Bus internal |
| PIN 6                    | 0 V          |
| Family construction form | 7/8"         |
| Gender                   | male         |
| Color contact carrier    | black        |
| No. of poles             | 5            |
| PIN 1                    | 0 V          |
| PIN 2                    | 0 V          |
| PIN 3                    | PE           |
| PIN 4                    | 24 V DC (US) |
| PIN 5                    | 24 V DC (UA) |