


CUBE67+ I/O EXTENSION MODULE

4 multif. channels + RS232/485/MOVIMOT


Expansion module
DIO4 RS232/485 (E) - 4x M12 MOVIMOT®
Serial interface
Digital inputs/outputs (multifunctional)
Connection cables are in the online shop under "Connection Technology".
Housing fully potted.
Cube67+ modules can only be operated on Cube67+, EtherNet/IP, PROFIBUS + PROFINET bus nodes.

Link do produto

Ilustração



Produto pode diferir da imagem



General product information	
Compatible with:	56521; 56526
Dados comerciais	
ECLASS-6.0	27242604
ECLASS-6.1	27242604
ECLASS-7.0	27242604
ECLASS-8.0	27242604
ECLASS-9.0	27242604
ECLASS-10.1	27242604
ECLASS-11.1	27242604
ECLASS-12.0	27242604
ETIM-5.0	EC001601
Classificação fiscal	85389099
GTIN	4048879048132
Quantidade por embalagem	1
Electrical data Supply	
Norm operating voltage	EN 61131-2
Operating voltage US DC	24 V

Operating voltage UA DC	24 V
Current consumption max.	80 mA
Total current UA max.	4 A
Total current US max.	4 A

Electrical data | Input

Overload resistant	yes
Short-circuit protected	yes
Type input	PNP, for 3-wire sensors or mechanical switches
Input filter time	1 ms
Sensor current US per input max.	0,2 A

Electrical data | Output

Overload resistant	yes
Short-circuit protected	yes
Output current per pin max.	0,5 A
Lamp load	10 W

Industrial communication

Data transmission rate max.	230,4 KBit/s
-----------------------------	--------------

Industrial communication | Ethernet functionality

duplex	Full or half duplex
--------	---------------------

Diagnostics

Actuator warning	per channel via LED and BUS
Diagnostic	No voltage, Under voltage
Diagnostic via BUS	per module and channel
Diagnostic via LED	per module and channel
Short circuit diagnosis	yes
LED display	Ethernet connection/data traffic
Overload diagnosis	yes

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP67
-------------------------------------	------

Mechanical data | Mounting data

Suitable for mounting type	2-hole screw mounting
Height	151 mm
Width	30 mm
Depth	34,5 mm

Environmental characteristics | Climatic

Operating temperature min.	0 °C
Operating temperature max.	55 °C
Storage temperature min.	-20 °C
Storage temperature max.	75 °C

Connection type 5

Connection type 1	Bus In
Connection type 2	Bus Out
Connection type 3	I / O
Connection type 4	RS232
Connection type 5	RS485
Family construction form	M12
Gender	male
Color contact carrier	black
Coding	A
No. of poles	6

PIN 1	24 V DC (UA)
PIN 2	24 V DC (US)
PIN 3	0 V
PIN 4	Bus internal
PIN 5	Bus internal
PIN 6	0 V
Family construction form	M12
Gender	female
Color contact carrier	black
Coding	A
No. of poles	6
PIN 1	24 V DC (UA)
PIN 2	24 V DC (US)
PIN 3	0 V
PIN 4	Bus internal
PIN 5	Bus internal
PIN 6	0 V
Family construction form	M12
Gender	female
Color contact carrier	black
Coding	A
No. of poles	5
PIN 1	24 V DC
PIN 2	DI / DO / Diag
PIN 3	0 V
PIN 4	DI / DO
PIN 5	FE
Family construction form	M12
Gender	female
Color contact carrier	black
Coding	B
No. of poles	5
PIN 1	RTS
PIN 2	TXD
PIN 3	0 V (separated)
PIN 4	RXD
PIN 5	CTS
Family construction form	M12
Gender	female
Color contact carrier	black
Coding	B
No. of poles	5
PIN 1	24 V DC
PIN 2	RS -
PIN 3	0 V
PIN 4	RS +
PIN 5	FE