

CUBE20S ANALOG INPUT MODULE AI4

4x16Bit R/RTD (0 .. 3000 Ohm) 12 Parameter Bytes


Expansion module
AI4 - (E) RTD 2-,3-wire
Requires less parameter bytes as item no: 57265
for resistors and temperature

Link do produto

Ilustração



Produto pode diferir da imagem



Dados comerciais	
ECLASS-6.0	27242601
ECLASS-6.1	27242601
ECLASS-7.0	27242601
ECLASS-8.0	27242601
ECLASS-9.0	27242601
ECLASS-10.1	27242601
ECLASS-11.1	27242601
ECLASS-12.0	27242601
ETIM-5.0	EC001596
Classificação fiscal	85389099
GTIN	4048879424042
Quantidade por embalagem	1
Electrical data Supply	
Operating voltage DC	24 V
Current consumption max.	55 mA
module supply	via system connection
Electrical data Input	
Type input	Pt100, Pt1000, Ni100, Ni1000, R 0...3000 Ω
Conversion time analog input per channel max.	324,1 ms
Diagnostics	

Diagnostic	Under voltage
Diagnostic via BUS	per module
Diagnostic via LED	per module and channel
Short circuit diagnosis	yes
LED display	Ethernet connection/data traffic
Overload diagnosis	yes
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP20
Mechanical data Mounting data	
Mounting method	geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	109 mm
Width	12,9 mm
Depth	76,5 mm
Environmental characteristics Climatic	
Operating temperature min.	0 °C
Operating temperature max.	60 °C
Storage temperature min.	-25 °C
Storage temperature max.	70 °C
Conformity	
Product standard	EN 61131-2
Connection type 2	
Connection type 1	Power
Connection type 2	Power
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
No. of poles	8
PIN 1	n.c.
PIN 2	24 V DC
PIN 3	0 V
PIN 4	24 V DC Sys
PIN 5	n.c.
PIN 6	24 V DC
PIN 7	0 V
PIN 8	0 V Sys
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
No. of poles	8
PIN 1	+ AI 0
PIN 2	- AI 0
PIN 3	+ AI 2
PIN 4	- AI 2
PIN 5	+ AI 1
PIN 6	- AI 1
PIN 7	+ AI 3
PIN 8	- AI 3