

MOTOR SUPPRESSOR

Varistor, 3x400VAC/20kW

3× 400 V AC



VDR

For DIN-rail mounting use Art.-No. 20900 adapter feet

Suppressors for other voltages, frequencies, and motor ratings available on request. Do not use RC motor suppressors with frequency inverters.

Link do produto

Ilustração



Produto pode diferir da imagem



| Dados comerciais |          |
|------------------|----------|
| ECLASS-6.0       | 27371013 |
| ECLASS-6.1       | 27371013 |
| ECLASS-7.0       | 27371013 |
| ECLASS-8.0       | 27371013 |
| ECLASS-9.0       | 27371013 |

|                                                      |                                                      |
|------------------------------------------------------|------------------------------------------------------|
| ECLASS-10.1                                          | 27371013                                             |
| ECLASS-11.1                                          | 27371013                                             |
| ECLASS-12.0                                          | 27371013                                             |
| ETIM-5.0                                             | EC000197                                             |
| Classificação fiscal                                 | 85363010                                             |
| GTIN                                                 | 4048879019255                                        |
| Quantidade por embalagem                             | 1                                                    |
| <b>Electrical data   Supply</b>                      |                                                      |
| Power frequency                                      | 10 ... 400 Hz                                        |
| <b>Electrical data   Input</b>                       |                                                      |
| Input voltage AC                                     | 400 V                                                |
| <b>Installation</b>                                  |                                                      |
| Connection cross-section stranded/fine-stranded min. | 0,35 mm²                                             |
| <b>Installation   Connection</b>                     |                                                      |
| Connection information                               | Einzellitzen mit selbstsicherndem Gabelkabelschuh M4 |
| Length single strands                                | 200 mm                                               |
| <b>Device protection   Media</b>                     |                                                      |
| Flame resistance                                     | flame retardant                                      |
| <b>Mechanical data   Material data</b>               |                                                      |
| Combustibility class housing (UL94)                  | V-0                                                  |
| Material housing                                     | Plastic                                              |
| Material potting compound                            | 2-component epoxy                                    |
| <b>Mechanical data   Mounting data</b>               |                                                      |
| Mounting method                                      | geschnappt                                           |
| Suitable for mounting type                           | Mounting rail TH35, (EN 60715)                       |
| Height                                               | 43 mm                                                |
| Width                                                | 15 mm                                                |
| Depth                                                | 40 mm                                                |
| <b>Environmental characteristics   Climatic</b>      |                                                      |
| Operating temperature min.                           | -20 °C                                               |
| Operating temperature max.                           | 60 °C                                                |