

**M12 male 0° A-cod. with cable**

PUR 5x0.34 ye UL/CSA 1.5m

Male straight

**⚠ NOTICE ⚠****PRODUCT IS DISCONTINUED. PLEASE HAVE A LOOK AT THE ALTERNATIVE PRODUCTS.**

A-coded





M12, 5-pole

Art-No. 7005 - M12 Lite - (plastic hexagonal screw) on request

Further cable lengths on request.

The resistance to aggressive media should be individually tested for your application. Further details on request.

Plastic housings with good resistance against chemicals and oils.

**Link do produto****Ilustração**

Produto pode diferir da imagem



Cable length 1,5 m

#### Side 1

|                                           |                   |
|-------------------------------------------|-------------------|
| Tightening torque                         | 0,6 Nm            |
| Mounting method                           | inserted, screwed |
| Family construction form                  | M12               |
| Thread                                    | M12 x 1           |
| suitable for corrugated tube (internal Ø) | 10 mm             |
| Coding                                    | A                 |
| Material                                  | PUR               |
| Width across flats                        | SW13              |
| Degree of protection (EN IEC 60529)       | IP65, IP66K, IP67 |

#### Side 2

Stripping length (jacket) 20 mm

#### Dados comerciais

|                          |               |
|--------------------------|---------------|
| ECLASS-6.0               | 27279218      |
| ECLASS-6.1               | 27279218      |
| ECLASS-7.0               | 27279218      |
| ECLASS-8.0               | 27279218      |
| ECLASS-9.0               | 27060311      |
| ECLASS-10.1              | 27060311      |
| ECLASS-11.1              | 27060311      |
| ECLASS-12.0              | 27060311      |
| ETIM-5.0                 | EC001855      |
| Classificação fiscal     | 85444290      |
| GTIN                     | 4048879217583 |
| Quantidade por embalagem | 1             |

#### Electrical data | Supply

|                                    |       |
|------------------------------------|-------|
| Operating voltage AC max.          | 125 V |
| Operating voltage DC max.          | 125 V |
| Operating voltage AC (UL-listed)   | 30 V  |
| Operating voltage DC (UL-listed)   | 30 V  |
| Current operating per contact max. | 4 A   |

#### Installation | Connection

|                           |         |
|---------------------------|---------|
| Stripping length (jacket) | 20 mm   |
| Mounting set              | M12 x 1 |

#### Device protection | Electrical

|                                        |                   |
|----------------------------------------|-------------------|
| Additional condition protection degree | inserted, screwed |
| Pollution Degree                       | 3                 |
| Rated surge voltage                    | 1,5 kV            |
| Material group (IEC 60664-1)           | I                 |

#### Mechanical data | Material data

|                           |                  |
|---------------------------|------------------|
| Coating locking           | Nickeled         |
| Coating of fitting        | nickel plated    |
| Locking material          | Zinc die-casting |
| Material screw connection | Zinc die-casting |

#### Mechanical data | Mounting data

Mounting method inserted, screwed, Shaking protection

#### Environmental characteristics | Climatic

|                                        |                            |
|----------------------------------------|----------------------------|
| Operating temperature min.             | -25 °C                     |
| Operating temperature max.             | 85 °C                      |
| Additional condition temperature range | depending on cable quality |

| Important installation notes                    |                                                                                                                                                       |
|-------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|
| Note on strain relief                           | Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.                                                   |
| Note on bending radius                          | <b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces. |
| Conformity                                      |                                                                                                                                                       |
| Product standard                                | DIN EN 61076-2-101 (M12)                                                                                                                              |
| Installation   Cable                            |                                                                                                                                                       |
| Cable identification                            | 834                                                                                                                                                   |
| Jacket Color                                    | blue                                                                                                                                                  |
| Type of Certificate                             | cURus                                                                                                                                                 |
| Amount stranding                                | 1                                                                                                                                                     |
| Stranding                                       | 2 wires twisted                                                                                                                                       |
| Amount stranding (type 2)                       | 1                                                                                                                                                     |
| Stranding (type 2)                              | 2 Stranded joints twisted                                                                                                                             |
| Cable shielding (type)                          | copper braid, tinned                                                                                                                                  |
| Cable shielding (coverage)                      | 65 %                                                                                                                                                  |
| Banding                                         | Foil                                                                                                                                                  |
| Drain wire (cross-section)                      | 22 AWG                                                                                                                                                |
| wire arrangement                                | (white, blue), (black, red)                                                                                                                           |
| Cable weight                                    | 63,12 g/m                                                                                                                                             |
| Material jacket                                 | PUR                                                                                                                                                   |
| Shore hardness jacket                           | 90 ± 5 Shore A                                                                                                                                        |
| Freedom from ingredients (jacket)               | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free                                                                                        |
| Outer-diameter (jacket)                         | 6,9 mm                                                                                                                                                |
| Tolerance outer diameter (sheath)               | ± 5 %                                                                                                                                                 |
| Material wire insulation                        | PE                                                                                                                                                    |
| Amount wires                                    | 2                                                                                                                                                     |
| Outer diameter insulation                       | 2,1 mm                                                                                                                                                |
| Outer diameter tolerance core insulation        | ± 5 %                                                                                                                                                 |
| Shore hardness wire insulation                  | 64 ± 5 Shore D                                                                                                                                        |
| Ingredient freeness wire insulation             | lead-free, CFC-free, halogen-free                                                                                                                     |
| Amount strands (wire)                           | 19                                                                                                                                                    |
| Diameter of single wires                        | 24 AWG                                                                                                                                                |
| Conductor crosssection (wire)                   | 24 AWG                                                                                                                                                |
| Drain wire (cross-section)                      | 22 AWG                                                                                                                                                |
| Material conductor wire                         | copper stranded wire, tinned                                                                                                                          |
| Electrical function wire                        | Data                                                                                                                                                  |
| Material wire insulation (Data)                 | PE                                                                                                                                                    |
| Outer diameter wire insulation (Data)           | 1,5 mm                                                                                                                                                |
| Tolerance outer diameter wire insulation (data) | ± 53 %                                                                                                                                                |
| Ingredient freeness wire insulation (Data)      | lead-free, CFC-free, halogen-free                                                                                                                     |
| Amount wires (Data)                             | 2                                                                                                                                                     |
| Amount strands wire (Data)                      | 19                                                                                                                                                    |
| Diameter of single wires (Data)                 | 22 AWG                                                                                                                                                |
| Conductor crosssection wire (Data)              | 22 AWG                                                                                                                                                |
| Material conductor wire (Data)                  | copper stranded wire, tinned                                                                                                                          |
| Electrical function wire (data)                 | Power                                                                                                                                                 |
| Traversing distance (C-track)                   | 5 m                                                                                                                                                   |
| Nominal voltage AC max.                         | 300 V                                                                                                                                                 |
| Current load capacity (standard)                | to DIN VDE 0298-4                                                                                                                                     |
| Current load capacity min. wire                 | 4,5 A                                                                                                                                                 |
| Current load capacity min. Wire (Data)          | 6 A                                                                                                                                                   |
| Electrical function wire                        | Data                                                                                                                                                  |

|                                           |                                                      |
|-------------------------------------------|------------------------------------------------------|
| Electrical function wire (data)           | Power                                                |
| Characteristic impedance                  | 120 $\Omega \pm 10\%$ @ 1 MHz                        |
| Electrical resistance line constant wire  | 78 $\Omega/\text{km}$                                |
| Electrical resistance coating wire (Data) | 54 $\Omega/\text{km}$                                |
| AC withstand voltage (wire - wire)        | 2 kV @ 60 s                                          |
| Electric capacitance                      | 40000 pF/km                                          |
| AC withstand voltage (wire - shield)      | 2 kV @ 60 s                                          |
| Min. operating temperature (static)       | -40 °C                                               |
| Max. operating temperature (fixed)        | 80 °C                                                |
| Operating temperature min. (dynamic)      | -30 °C                                               |
| Operating temperature max. (dynamic)      | 70 °C                                                |
| Flame resistance                          | UL 1581 § 1100 FT2   UL 1581 § 1090   IEC 60332-2-2  |
| chemical resistance                       | Good, application-related testing                    |
| Gasoline resistance                       | Good, application-related testing                    |
| Oil resistance                            | Good, application-related testing   DIN EN 60811-404 |
| Bending radius (installation)             | x Outer diameter                                     |
| Bending radius (fixed)                    | 6 x Outer diameter                                   |
| Bending radius (dynamic)                  | 10 x Outer diameter                                  |
| Travel speed (C-track)                    | 1 Mio.                                               |
| No. of torsion cycles                     | 2 Mio.                                               |
| Torsion stress                            | $\pm 30^\circ/\text{m}$                              |
| Torsion speed                             | 35 cycles/min                                        |