

MA5I67 I/O MODULE

8 digital inputs


Digital inputs
DI8 - 0.24 A - 4× M12 (AB)
Double assignment of M12 females, PIN 2 + 4
Connection cables are in the online shop under "Connection Technology".
Housing fully potted.

Link do produto

Ilustração



Produto pode diferir da imagem



Dados comerciais	
ECLASS-6.0	27242604
ECLASS-6.1	27242604
ECLASS-7.0	27242604
ECLASS-8.0	27242604
ECLASS-9.0	27242604
ECLASS-10.1	27242604
ECLASS-11.1	27242604
ECLASS-12.0	27242604
ETIM-5.0	EC001599
Classificação fiscal	85176200
GTIN	4048879049108
Quantidade por embalagem	1
Electrical data Supply	
Bus voltage AS-Interface DC min.	26,5 V
Bus voltage AS-Interface DC max.	31,6 V
Current consumption AS-i port max.	290 mA
Electrical data Input	
Overload resistant	yes
Short-circuit protected	yes

Type input	PNP, for 3-wire sensors or mechanical switches
------------	--

Current carrying capacity max.	0,24 A
--------------------------------	--------

Industrial communication | Bus data

Address setting type	Addressing socket, Master
----------------------	---------------------------

Slave address range	(0), 1 A...31 A, 1 B...31 B
---------------------	-----------------------------

Industrial communication | AS-Interface

Profile (IO.ID.ID2)	2x S-0.A.2
---------------------	------------

Diagnostics

Diagnostic	No voltage
------------	------------

Diagnostic via LED	per module
--------------------	------------

LED display	Ethernet connection/data traffic
-------------	----------------------------------

Installation | Connection

Double assignment M12 female	yes
------------------------------	-----

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP67
-------------------------------------	------

Mechanical data | Mounting data

Mounting method	screwed, geschnappt
-----------------	---------------------

Suitable for mounting type	mounting rail, (EN 60715)
----------------------------	---------------------------

Height	94 mm
--------	-------

Width	60 mm
-------	-------

Depth	39 mm
-------	-------

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
----------------------------	--------

Operating temperature max.	60 °C
----------------------------	-------

Storage temperature min.	-20 °C
--------------------------	--------

Storage temperature max.	70 °C
--------------------------	-------

Connection type 1

Connection type 1	C D
-------------------	-----

Family construction form	M12
--------------------------	-----

Gender	female
--------	--------

Color contact carrier	black
-----------------------	-------

Coding	A
--------	---

No. of poles	5
--------------	---

PIN 1	Usens +
-------	---------

PIN 2	DI
-------	----

PIN 3	Usens -
-------	---------

PIN 4	DI
-------	----

PIN 5	n.c.
-------	------