

MASI67 I/O MODULE

4 digital inputs, 4 digital outputs


Digital inputs/outputs
DI4 - 1.6 A DO4 - 2 A - 4× M12
Double assignment of M12 females, PIN 2 + 4
Sensor supply from external 24 V DC
Connection cables are in the online shop under "Connection Technology".
Housing fully potted.

Link do produto

Ilustração



Produto pode diferir da imagem



Dados comerciais	
ECLASS-6.0	27242604
ECLASS-6.1	27242604
ECLASS-7.0	27242604
ECLASS-8.0	27242604
ECLASS-9.0	27242604
ECLASS-10.1	27242604
ECLASS-11.1	27242604
ECLASS-12.0	27242604
ETIM-5.0	EC001599
Classificação fiscal	85176200
GTIN	4048879049078
Quantidade por embalagem	1
Electrical data Supply	
Norm operating voltage	EN 61131-2
Operating voltage UA DC	24 V
Operating voltage UA DC min.	18 V
Operating voltage UA DC max.	30,2 V
Bus voltage AS-Interface DC min.	26,5 V
Bus voltage AS-Interface DC max.	31,6 V

As informações contidas nesta folha de dados foram elaboradas com o máximo cuidado.
A falta de integridade, exatidão e atualização das informações é considerada negligência grave. versão: 27/04/2024
Murrelektronik GmbH | Falkenstraße 3 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

Current consumption AS-i port max.	50 mA
Total current max.	8 A
Electrical data Input	
Overload resistant	yes
Short-circuit protected	yes
Type input	PNP, for 3-wire sensors or mechanical switches
Current carrying capacity max.	1,6 A
Electrical data Output	
Overload resistant	yes
Short-circuit protected	yes
Output current per pin max.	2 A
Industrial communication Bus data	
Address setting type	Addressing socket, Master
Slave address range	(0), 1 ...
Industrial communication AS-Interface	
Profile (IO.ID.ID2)	S-7.F.E
Diagnostics	
Diagnostic	No voltage
Diagnostic via LED	per module
LED display	Ethernet connection/data traffic
Installation Connection	
Double assignment M12 female	yes
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP67
Mechanical data Mounting data	
Mounting method	screwed, geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	94 mm
Width	60 mm
Depth	39 mm
Environmental characteristics Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	60 °C
Storage temperature min.	-20 °C
Storage temperature max.	70 °C
Connection type 1	
Connection type 1	0-3
Family construction form	M12
Gender	female
Color contact carrier	black
Coding	A
No. of poles	5
PIN 1	Usens +
PIN 2	DI
PIN 3	Usens -
PIN 4	DI
PIN 5	n.c.