


MA5I68 I/O EXTENSION MODULE

4 analog Inputs U/I configurable


AI4 - (E) 4× M12 (UI)
Connection cables are in the online shop under "Connection Technology".
Housing fully potted.

Link do produto

Ilustração



Produto pode diferir da imagem



Dados comerciais	
ECLASS-6.0	27242601
ECLASS-6.1	27242601
ECLASS-7.0	27242601
ECLASS-8.0	27242601
ECLASS-9.0	27242601
ECLASS-10.1	27242601
ECLASS-11.1	27242601
ECLASS-12.0	27242601
ETIM-5.0	EC001596
Classificação fiscal	85176200
GTIN	4048879496681
Quantidade por embalagem	1
Electrical data Supply	
Norm operating voltage	EN 61131-2
Operating voltage US DC	24 V
Bus voltage AS-Interface DC min.	26,5 V
Bus voltage AS-Interface DC max.	31,6 V
Current consumption AS-i port max.	100 mA
Electrical data Input	
Overload resistant	yes
Short-circuit protected	yes

As informações contidas nesta folha de dados foram elaboradas com o máximo cuidado.
A falta de integridade, exatidão e atualização das informações é considerada negligência grave. versão: 10/05/2024

Sensor current US per input max. 0,1 A

Industrial communication | Bus data

Address setting type M12 connection and programming device, Master
Slave address range 1 ... 31

Industrial communication | AS-Interface

Profile (IO.ID.ID2) S-7.3.E

Diagnostics

Diagnostic No voltage
Diagnostic via LED per module
LED display Ethernet connection/data traffic

Device protection | Electrical

Degree of protection (EN IEC 60529) IP68

Mechanical data | Mounting data

Mounting method screwed
Height 151 mm
Width 30 mm
Depth 34,5 mm

Environmental characteristics | Climatic

Operating temperature min. -20 °C
Operating temperature max. 70 °C
Storage temperature min. -40 °C
Storage temperature max. 85 °C

Connection type 3

Connection type 1 0-3
Connection type 2 Bus In
Connection type 3 Bus Out
Family construction form M12
Gender female
Color contact carrier black
Coding A
No. of poles 5
PIN 1 24 V DC
PIN 2 In +
PIN 3 0 V
PIN 4 In -
PIN 5 n.c.
Family construction form M12
Gender male
Color contact carrier black
Coding A
No. of poles 4
PIN 1 AS-i +
PIN 2 0 V
PIN 3 AS-i -
PIN 4 24 V DC
Family construction form M12
Gender female
Color contact carrier black
Coding A
No. of poles 5
PIN 1 AS-i +

PIN 2	0 V
PIN 3	AS-i -
PIN 4	24 V DC
PIN 5	n.c.