

MA5I68 I/O EXTENSION MODULE

2 analog Outputs U/I configurable


AO2 - (E) 2× M12 (UI)
Connection cables are in the online shop under "Connection Technology".
Housing fully potted.

Link do produto

Ilustração



Produto pode diferir da imagem



Dados comerciais	
ECLASS-6.0	27242604
ECLASS-6.1	27242604
ECLASS-7.0	27242604
ECLASS-8.0	27242604
ECLASS-9.0	27242604
ECLASS-10.1	27242604
ECLASS-11.1	27242604
ECLASS-12.0	27242604
ETIM-5.0	EC001599
Classificação fiscal	85176200
GTIN	4048879611183
Quantidade por embalagem	1
Electrical data Supply	
Norm operating voltage	EN 61131-2
Operating voltage UA DC	24 V
Operating voltage UA DC min.	18 V
Operating voltage UA DC max.	30,2 V
Bus voltage AS-Interface DC min.	26,5 V
Bus voltage AS-Interface DC max.	31,6 V
Current consumption AS-i port max.	100 mA
Electrical data Output	

Working resistance max.	60 Ω
-------------------------	------

Load resistance min.	1 kΩ
----------------------	------

Conversion time analog output max.	1,5 ms
------------------------------------	--------

Industrial communication | Bus data

Address setting type	M12 connection and programming device, Master
----------------------	---

Slave address range	(0), 1 ...
---------------------	------------

Industrial communication | AS-Interface

Profile (IO.ID.ID2)	S-7.3.5
---------------------	---------

Diagnostics

Diagnostic	No voltage
------------	------------

Diagnostic via LED	per module
--------------------	------------

LED display	Ethernet connection/data traffic
-------------	----------------------------------

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP68
-------------------------------------	------

Mechanical data | Mounting data

Mounting method	screwed
-----------------	---------

Height	126 mm
--------	--------

Width	30 mm
-------	-------

Depth	34,5 mm
-------	---------

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
----------------------------	--------

Operating temperature max.	60 °C
----------------------------	-------

Storage temperature min.	-20 °C
--------------------------	--------

Storage temperature max.	70 °C
--------------------------	-------

Connection type 3

Connection type 1	A B
-------------------	-----

Connection type 2	Bus In
-------------------	--------

Connection type 3	Bus Out
-------------------	---------

Family construction form	M12
--------------------------	-----

Gender	female
--------	--------

Color contact carrier	black
-----------------------	-------

Coding	A
--------	---

No. of poles	5
--------------	---

PIN 1	AO +
-------	------

PIN 2	n.c.
-------	------

PIN 3	AO -
-------	------

PIN 4	n.c.
-------	------

PIN 5	PE
-------	----

Family construction form	M12
--------------------------	-----

Gender	male
--------	------

Color contact carrier	black
-----------------------	-------

Coding	A
--------	---

No. of poles	4
--------------	---

PIN 1	AS-i +
-------	--------

PIN 2	0 V
-------	-----

PIN 3	AS-i -
-------	--------

PIN 4	24 V DC
-------	---------

Family construction form	M12
--------------------------	-----

Gender	female
--------	--------

Color contact carrier	black
-----------------------	-------

Coding	A
--------	---

No. of poles	5
PIN 1	AS-i +
PIN 2	0 V
PIN 3	AS-i -
PIN 4	24 V DC
PIN 5	n.c.