

MVP12-P6 DIO16CGND 8xM12A IOL_12 E0

IO-Link Hub


IO-Link hub in 50 mm plastic housing
16 digital inputs and 16 digital outputs
1 × M12 IO-Link
8 × M12 I/O
Extended parameter range
Connection cables are in the online shop under "Connection Technology".

Link do produto

Ilustração



Produto pode diferir da imagem



Electrical data Supply	
Operating voltage DC	24 V
Operating voltage US DC	24 V
Operating voltage US DC min.	18 V
Operating voltage US DC max.	30 V
Operating voltage UA DC	24 V
Operating voltage UA DC min.	18 V
Operating voltage UA DC max.	30 V
Current consumption max.	50 mA
Total current UA max.	4 A
Total current US max.	4 A
Electrical data Input	
Sensor current per input max.	0,5 A
Type input	Type 1, Type 3
Input time filter min.	1 ms
Input time filter max.	10 ms
Input time filter parameterizable	yes
Electrical data Output	
Output current per pin max.	2 A

Industrial communication IO-Link	
IO-Link type	Device
IO-Link revision ID	V1.1.2
IO-Link transmission rate	COM3 (230.4 kbit/s)
IO-Link process data length input	4 Bytes
IO-Link process data length output	2 Bytes
IO-Link cycle time min.	1 ms
IO-Link revision compatibility	V1.1.3
Diagnostics	
Actuator warning	yes
Diagnostic via LED	per module and channel
IO-Link events	No voltage, Undervoltage supply
Short circuit diagnosis	yes
LED display	Ethernet connection/data traffic
Status indication LED	green
Overload diagnosis	yes
Device protection Electrical	
Installation height max. ASL	3000 m
Degree of protection (EN IEC 60529)	IP68
Overload resistant	yes
Short-circuit protected	yes
Galvanic separation US/UA	no
Mechanical data Mounting data	
Suitable for mounting type	2-hole screw mounting
Height	126 mm
Width	50 mm
Depth	34,5 mm
Environmental characteristics Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	70 °C
Storage temperature min.	-40 °C
Storage temperature max.	85 °C
Conformity	
Product standard	EN 61131-2
Connection type 4	
Connection type 1	X0-X7
Connection type 2	X4-X7
Connection type 3	XZ1
Connection type 4	XZ1
Family construction form	M12
Gender	female
Color contact carrier	black
Coding	A
No. of poles	5
PIN 1	24 V DC (US) (L +)
PIN 2	DIO
PIN 3	0 V
PIN 4	DIO
PIN 5	n.c.
Family construction form	M12
Gender	female
Coding	A

No. of poles	5
PIN 1	24 V DC US (L +)
PIN 2	DIO
PIN 3	0 V
PIN 4	DIO
PIN 5	PE
Family construction form	M12
Gender	male
Coding	A
No. of poles	5
PIN 1	24 V DC US (L +)
PIN 2	24 V DC UA (P 24)
PIN 3	0 V
PIN 4	C / Q / IO-Link
PIN 5	0 V
Family construction form	M12
Gender	male
Coding	A
No. of poles	5
PIN 1	24 V DC (US) (L +)
PIN 2	24 V DC (UA) (P 24)
PIN 3	0 V
PIN 4	C / Q / IO-Link
PIN 5	0 V
Dados comerciais	
Classificação fiscal	85389099
GTIN	4065909035481
Quantidade por embalagem	1