




**MIRO 6.2 OUTPUT RELAY WITH TOGGLE SWITCH**

IN: 24 VAC/DC - OUT: 250 VAC/DC / 6 A

1 NO contact  
 6 A  
 24 V AC/DC  
 with protected H-O-A toggle switch  
 Screw terminals  
 LED (red/green)  
 safe separation (EN 60947-1)

[Link do produto](#)
**Ilustração**


Produto pode diferir da imagem


**Dados comerciais**

|            |          |
|------------|----------|
| ECLASS-6.0 | 27371601 |
| ECLASS-6.1 | 27371601 |
| ECLASS-7.0 | 27371601 |

|                          |               |
|--------------------------|---------------|
| ECLASS-8.0               | 27371601      |
| ECLASS-9.0               | 27371601      |
| ECLASS-10.1              | 27371601      |
| ECLASS-11.1              | 27371601      |
| ECLASS-12.0              | 27371601      |
| ETIM-5.0                 | EC001437      |
| Classificação fiscal     | 85364900      |
| GTIN                     | 4048879024693 |
| Quantidade por embalagem | 1             |

**Electrical data | Input**

|                       |        |
|-----------------------|--------|
| Input voltage AC      | 24 V   |
| Input voltage AC min. | 19,2 V |
| Input voltage AC max. | 28 V   |
| Input voltage DC      | 24 V   |
| Input voltage DC min. | 19,2 V |
| Input voltage DC max. | 28 V   |
| Input current         | 7 mA   |

**Electrical data | Output**

|                                               |                                          |
|-----------------------------------------------|------------------------------------------|
| Utilization category AC-12 (EN IEC 60947-5-1) | 6 A @ 24, 6 A @ 110 V, 6 A @ 230 V       |
| Utilization category AC-15 (EN IEC 60947-5-1) | 3 A @ 24 V, 3 A @ 110 V, 3 A @ 230 V     |
| Utilization category DC-13 (EN IEC 60947-5-1) | 1 A @ 24 V, 0,2 A @ 110 V, 0,1 A @ 230 V |
| Switching frequency max.                      | 10 Hz                                    |
| Power rating AC max.                          | 1500 VA                                  |
| Power rating DC max.                          | 120 W                                    |
| Switching voltage AC max.                     | 250 V                                    |
| Switching voltage DC max.                     | 250 V                                    |
| Switching current DC                          | 100 mA                                   |
| Switching current max.                        | 6 A                                      |

**Diagnostics**

|                       |            |
|-----------------------|------------|
| Status indication LED | green, red |
|-----------------------|------------|

**Device protection**

|                    |                |
|--------------------|----------------|
| Condition lifetime | load-dependent |
|--------------------|----------------|

**Device protection | Electrical**

|                     |                 |
|---------------------|-----------------|
| Rated surge voltage | 4 kV            |
| Electrical lifetime | 20000000 Cycles |

**Device protection | Mechanical**

|                      |                 |
|----------------------|-----------------|
| Mechanical endurance | 20000000 Cycles |
|----------------------|-----------------|

**Mechanical data**

|                    |       |
|--------------------|-------|
| Drop-out time max. | 20 ms |
| Response time max. | 8 ms  |
| Bounce time max.   | 2 ms  |

**Mechanical data | Material data**

|                  |          |
|------------------|----------|
| Material contact | Ag Sn O2 |
|------------------|----------|

**Mechanical data | Mounting data**

|                            |                           |
|----------------------------|---------------------------|
| Mounting method            | geschnappt                |
| Suitable for mounting type | mounting rail, (EN 60715) |
| Height                     | 91 mm                     |
| Width                      | 6,2 mm                    |
| Depth                      | 71 mm                     |

**Environmental characteristics | Climatic**

|                            |        |
|----------------------------|--------|
| Operating temperature min. | -20 °C |
|----------------------------|--------|

|                            |       |
|----------------------------|-------|
| Operating temperature max. | 55 °C |
|----------------------------|-------|

**Connection type 5**

|            |                    |
|------------|--------------------|
| Connection | Screw terminals SK |
|------------|--------------------|

|                          |          |
|--------------------------|----------|
| Family construction form | terminal |
|--------------------------|----------|

|        |        |
|--------|--------|
| Gender | female |
|--------|--------|

|                       |       |
|-----------------------|-------|
| Color contact carrier | black |
|-----------------------|-------|

|              |   |
|--------------|---|
| No. of poles | 1 |
|--------------|---|

|       |     |
|-------|-----|
| PIN 1 | A 2 |
|-------|-----|

|            |                    |
|------------|--------------------|
| Connection | Screw terminals SK |
|------------|--------------------|

|                          |          |
|--------------------------|----------|
| Family construction form | terminal |
|--------------------------|----------|

|        |        |
|--------|--------|
| Gender | female |
|--------|--------|

|                       |       |
|-----------------------|-------|
| Color contact carrier | black |
|-----------------------|-------|

|              |   |
|--------------|---|
| No. of poles | 1 |
|--------------|---|

|       |     |
|-------|-----|
| PIN 1 | A 3 |
|-------|-----|

|            |                    |
|------------|--------------------|
| Connection | Screw terminals SK |
|------------|--------------------|

|                          |          |
|--------------------------|----------|
| Family construction form | terminal |
|--------------------------|----------|

|        |        |
|--------|--------|
| Gender | female |
|--------|--------|

|                       |       |
|-----------------------|-------|
| Color contact carrier | black |
|-----------------------|-------|

|              |   |
|--------------|---|
| No. of poles | 1 |
|--------------|---|

|       |     |
|-------|-----|
| PIN 1 | A 1 |
|-------|-----|

|            |                    |
|------------|--------------------|
| Connection | Screw terminals SK |
|------------|--------------------|

|                          |          |
|--------------------------|----------|
| Family construction form | terminal |
|--------------------------|----------|

|        |        |
|--------|--------|
| Gender | female |
|--------|--------|

|                       |       |
|-----------------------|-------|
| Color contact carrier | black |
|-----------------------|-------|

|              |   |
|--------------|---|
| No. of poles | 1 |
|--------------|---|

|       |    |
|-------|----|
| PIN 1 | 14 |
|-------|----|

|            |                    |
|------------|--------------------|
| Connection | Screw terminals SK |
|------------|--------------------|

|                          |          |
|--------------------------|----------|
| Family construction form | terminal |
|--------------------------|----------|

|        |        |
|--------|--------|
| Gender | female |
|--------|--------|

|                       |       |
|-----------------------|-------|
| Color contact carrier | black |
|-----------------------|-------|

|              |   |
|--------------|---|
| No. of poles | 1 |
|--------------|---|

|       |    |
|-------|----|
| PIN 1 | 13 |
|-------|----|