

MIRO 6.2-1OUTPUT-REL.24V-1S-FK

MIRO 6.2 24V OUTPUT RELAY

- 1 NO contact
- 6 A
- 24 V AC/DC
- Spring clamp terminals
- safe separation (EN 60947-1)

Link do produto

Ilustração



Produto pode diferir da imagem



| Dados comerciais |          |
|------------------|----------|
| ECLASS-6.0       | 27371001 |
| ECLASS-6.1       | 27371601 |
| ECLASS-7.0       | 27371601 |
| ECLASS-8.0       | 27371601 |
| ECLASS-9.0       | 27371601 |

|                                                 |                                          |
|-------------------------------------------------|------------------------------------------|
| ECLASS-10.1                                     | 27371601                                 |
| ECLASS-11.1                                     | 27371601                                 |
| ECLASS-12.0                                     | 27371601                                 |
| ETIM-5.0                                        | EC001437                                 |
| Classificação fiscal                            | 85364900                                 |
| GTIN                                            | 4048879022163                            |
| Quantidade por embalagem                        | 1                                        |
| <b>Electrical data   Input</b>                  |                                          |
| Input voltage DC                                | 24 V                                     |
| Input voltage DC min.                           | 19,2 V                                   |
| Input voltage DC max.                           | 30 V                                     |
| Input current                                   | 17 mA                                    |
| <b>Electrical data   Output</b>                 |                                          |
| Utilization category AC-12 (EN IEC 60947-5-1)   | 6 A @ 24, 6 A @ 110 V, 6 A @ 230 V       |
| Utilization category AC-15 (EN IEC 60947-5-1)   | 3 A @ 24 V, 3 A @ 110 V, 3 A @ 230 V     |
| Utilization category DC-13 (EN IEC 60947-5-1)   | 1 A @ 24 V, 0,2 A @ 110 V, 0,1 A @ 230 V |
| Switching frequency max.                        | 10 Hz                                    |
| Power rating AC max.                            | 1500 VA                                  |
| Power rating DC max.                            | 120 W                                    |
| Switching voltage AC max.                       | 250 V                                    |
| Switching voltage DC max.                       | 250 V                                    |
| Switching current DC                            | 100 mA                                   |
| Switching current max.                          | 6 A                                      |
| <b>Diagnostics</b>                              |                                          |
| Status indication LED                           | green                                    |
| <b>Device protection</b>                        |                                          |
| Condition lifetime                              | load-dependent                           |
| <b>Device protection   Electrical</b>           |                                          |
| Rated surge voltage                             | 4 kV                                     |
| Electrical lifetime                             | 20000000 Cycles                          |
| <b>Device protection   Mechanical</b>           |                                          |
| Mechanical endurance                            | 20000000 Cycles                          |
| <b>Mechanical data</b>                          |                                          |
| Drop-out time max.                              | 15 ms                                    |
| Response time max.                              | 10 ms                                    |
| Bounce time max.                                | 1,5 ms                                   |
| <b>Mechanical data   Material data</b>          |                                          |
| Material contact                                | Ag Sn O2                                 |
| <b>Mechanical data   Mounting data</b>          |                                          |
| Mounting method                                 | geschnappt                               |
| Suitable for mounting type                      | mounting rail, (EN 60715)                |
| Height                                          | 78 mm                                    |
| Width                                           | 6,2 mm                                   |
| Depth                                           | 70 mm                                    |
| <b>Environmental characteristics   Climatic</b> |                                          |
| Operating temperature min.                      | -25 °C                                   |
| Operating temperature max.                      | 60 °C                                    |
| <b>Connection type 4</b>                        |                                          |
| Connection                                      | Spring clamp terminals FK                |
| Family construction form                        | terminal                                 |

|                          |                           |
|--------------------------|---------------------------|
| Gender                   | female                    |
| Color contact carrier    | black                     |
| No. of poles             | 1                         |
| PIN 1                    | 13                        |
| Connection               | Spring clamp terminals FK |
| Family construction form | terminal                  |
| Gender                   | female                    |
| Color contact carrier    | black                     |
| No. of poles             | 1                         |
| PIN 1                    | 14                        |
| Connection               | Spring clamp terminals FK |
| Family construction form | terminal                  |
| Gender                   | female                    |
| Color contact carrier    | black                     |
| No. of poles             | 1                         |
| PIN 1                    | A 1                       |
| Connection               | Spring clamp terminals FK |
| Family construction form | terminal                  |
| Gender                   | female                    |
| Color contact carrier    | black                     |
| No. of poles             | 1                         |
| PIN 1                    | A 2                       |