



**M12 male 0° A-cod. with cable shielded**

PUR 4x0.34 shielded gy 5m


Male straight  
M12, 4-pole  
A-coded  
shielded

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.  
Further cable lengths on request.

[Link do produto](#)**Ilustração**

Produto pode diferir da imagem



Cable length 5 m

**Side 1**

Tightening torque 0,6 Nm

As informações contidas nesta folha de dados foram elaboradas com o máximo cuidado.  
A falta de integridade, exatidão e atualização das informações é considerada negligência grave. versão: 21/05/2024

Murrelektronik GmbH | Falkenstraße 3 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

|                                     |                   |
|-------------------------------------|-------------------|
| Mounting method                     | inserted, screwed |
| Coating contact                     | gold plated       |
| Family construction form            | M12               |
| Thread                              | M12 x 1           |
| Coding                              | A                 |
| Material contact                    | Copper alloy      |
| Material                            | PUR               |
| No. of poles                        | 4                 |
| Width across flats                  | SW13              |
| Degree of protection (EN IEC 60529) | IP65, IP66K, IP67 |

**Side 2**

|                           |             |
|---------------------------|-------------|
| Stripping length (jacket) | 20 mm       |
| Coating contact           | gold plated |

**Dados comerciais**

|                          |               |
|--------------------------|---------------|
| ECLASS-6.0               | 27279218      |
| ECLASS-6.1               | 27279218      |
| ECLASS-7.0               | 27279218      |
| ECLASS-8.0               | 27279218      |
| ECLASS-9.0               | 27060311      |
| ECLASS-10.1              | 27060311      |
| ECLASS-11.1              | 27060311      |
| ECLASS-12.0              | 27060311      |
| ETIM-5.0                 | EC001855      |
| Classificação fiscal     | 85444290      |
| GTIN                     | 4048879201254 |
| Quantidade por embalagem | 1             |

**Electrical data | Supply**

|                                    |      |
|------------------------------------|------|
| Operating voltage AC max.          | 60 V |
| Operating voltage DC max.          | 60 V |
| Current operating per contact max. | 4 A  |

**Diagnostics**

|                       |    |
|-----------------------|----|
| Status indication LED | no |
|-----------------------|----|

**Installation | Connection**

|                           |         |
|---------------------------|---------|
| Stripping length (jacket) | 20 mm   |
| Mounting set              | M12 x 1 |

**Device protection | Electrical**

|                                        |                   |
|----------------------------------------|-------------------|
| Additional condition protection degree | inserted, screwed |
| Pollution Degree                       | 3                 |
| Rated surge voltage                    | 1,5 kV            |
| Material group (IEC 60664-1)           | I                 |

**Mechanical data | Material data**

|                           |                  |
|---------------------------|------------------|
| Coating locking           | Nickeled         |
| Coating of fitting        | nickel plated    |
| Locking material          | Zinc die-casting |
| Material screw connection | Zinc die-casting |

**Mechanical data | Mounting data**

|                 |                                       |
|-----------------|---------------------------------------|
| Mounting method | inserted, screwed, Shaking protection |
|-----------------|---------------------------------------|

**Environmental characteristics | Climatic**

|                                        |                            |
|----------------------------------------|----------------------------|
| Operating temperature min.             | -25 °C                     |
| Operating temperature max.             | 85 °C                      |
| Additional condition temperature range | depending on cable quality |

| Important installation notes                      |                                                                                                                                                       |
|---------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|
| Note on strain relief                             | Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.                                                   |
| Note on bending radius                            | <b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces. |
| Conformity                                        |                                                                                                                                                       |
| Product standard                                  | DIN EN 61076-2-101 (M12)                                                                                                                              |
| Installation   Cable                              |                                                                                                                                                       |
| wire arrangement                                  | brown, black, blue, white                                                                                                                             |
| Cable identification                              | 331                                                                                                                                                   |
| Jacket Color                                      | gray                                                                                                                                                  |
| Amount stranding                                  | 1                                                                                                                                                     |
| Stranding                                         | 4 wires twisted                                                                                                                                       |
| Banding                                           | Fleece, Foil                                                                                                                                          |
| wire arrangement                                  | brown, black, blue, white                                                                                                                             |
| Material jacket                                   | PUR                                                                                                                                                   |
| Shore hardness jacket                             | 85 $\pm$ 5 Shore A                                                                                                                                    |
| Freedom from ingredients (jacket)                 | lead-free, cadmium-free, CFC-free, silicone-free                                                                                                      |
| Outer-diameter (jacket)                           | 5,9 mm                                                                                                                                                |
| Tolerance outer diameter (sheath)                 | $\pm$ 5 %                                                                                                                                             |
| Material inner jacket                             | PVC                                                                                                                                                   |
| Color (inner jacket)                              | gray                                                                                                                                                  |
| Material wire insulation                          | PVC                                                                                                                                                   |
| Amount wires                                      | 4                                                                                                                                                     |
| Outer diameter insulation                         | 1,4 mm                                                                                                                                                |
| Outer diameter tolerance core insulation          | $\pm$ 5 %                                                                                                                                             |
| Shore hardness wire insulation                    | 85 $\pm$ 5 Shore A                                                                                                                                    |
| Ingredient freeness wire insulation               | lead-free, cadmium-free, CFC-free, silicone-free                                                                                                      |
| Amount strands (wire)                             | 42                                                                                                                                                    |
| Diameter of single wires                          | 0,1 mm                                                                                                                                                |
| Conductor crosssection (wire)                     | 0,34 mm <sup>2</sup>                                                                                                                                  |
| Material conductor wire                           | Stranded copper wire, bare                                                                                                                            |
| Conductor type (wire)                             | strand class 6                                                                                                                                        |
| Max. rated voltage (conductor - conductor)        | 350 V                                                                                                                                                 |
| Max. rated voltage (conductor - ground)           | 300 V                                                                                                                                                 |
| Current load capacity (standard)                  | to DIN VDE 0298-4                                                                                                                                     |
| Current load capacity min. wire                   | 4,8 A                                                                                                                                                 |
| Electrical resistance line constant wire          | 57 $\Omega$ /km @ 20 °C                                                                                                                               |
| AC withstand voltage (wire - wire)                | 2 kV @ 60 s                                                                                                                                           |
| Power frequency withstand voltage (wire - jacket) | 2 kV @ 60 s                                                                                                                                           |
| AC withstand voltage (wire - shield)              | 1,5 kV @ 60 s                                                                                                                                         |
| Min. operating temperature (static)               | -30 °C                                                                                                                                                |
| Max. operating temperature (fixed)                | 80 °C                                                                                                                                                 |
| Operating temperature min. (dynamic)              | -5 °C                                                                                                                                                 |
| Operating temperature max. (dynamic)              | 70 °C                                                                                                                                                 |
| Flame resistance                                  | UL 1581 § 1100 FT2   IEC 60332-2-2   UL 1581 § 1090                                                                                                   |
| chemical resistance                               | Good, application-related testing                                                                                                                     |
| Gasoline resistance                               | Good, application-related testing                                                                                                                     |
| Oil resistance                                    | Good, application-related testing   DIN EN 60811-404                                                                                                  |
| Bending radius (installation)                     | x Outer diameter                                                                                                                                      |
| Bending radius (fixed)                            | 10 x Outer diameter                                                                                                                                   |
| Bending radius (dynamic)                          | 15 x Outer diameter                                                                                                                                   |
| No. of bending cycles (C-track)                   | 0,1 Mio. @ 25 °C                                                                                                                                      |
| Traversing distance (C-track)                     | 5 m @ 25 °C                                                                                                                                           |

Travel speed (C-track)

3 m/s @ 25 °C