

**M12 male 90° B-cod. with cable shielded**

PVC 1x2xAWG24 shielded vt UL/CSA 10m

## PROFIBUS

Male 90°

M12, 2-pole



B-coded

shielded


Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

Further cable lengths on request.

[Link do produto](#)**Ilustração**

Produto pode diferir da imagem



Cable length

10 m

**Side 1**

|                                     |                   |
|-------------------------------------|-------------------|
| Tightening torque                   | 0,6 Nm            |
| Mounting method                     | inserted, screwed |
| Family construction form            | M12               |
| Thread                              | M12 x 1           |
| Material                            | PUR               |
| Width across flats                  | SW13              |
| Degree of protection (EN IEC 60529) | IP65, IP66K, IP67 |

**Dados comerciais**

|                          |               |
|--------------------------|---------------|
| ECLASS-6.0               | 27061801      |
| ECLASS-6.1               | 27060307      |
| ECLASS-7.0               | 27060307      |
| ECLASS-8.0               | 27060307      |
| ECLASS-9.0               | 27060307      |
| ECLASS-10.1              | 27060307      |
| ECLASS-11.1              | 27060307      |
| ECLASS-12.0              | 27060307      |
| ETIM-5.0                 | EC001855      |
| Classificação fiscal     | 85444290      |
| GTIN                     | 4048879570541 |
| Quantidade por embalagem | 1             |

**Electrical data | Supply**

|                                    |      |
|------------------------------------|------|
| Operating voltage AC max.          | 60 V |
| Operating voltage DC max.          | 60 V |
| Operating voltage AC (UL-listed)   | 30 V |
| Operating voltage DC (UL-listed)   | 30 V |
| Current operating per contact max. | 4 A  |

**Installation | Connection**

|              |         |
|--------------|---------|
| Mounting set | M12 x 1 |
|--------------|---------|

**Device protection | Electrical**

|                                        |                   |
|----------------------------------------|-------------------|
| Additional condition protection degree | inserted, screwed |
|----------------------------------------|-------------------|

**Mechanical data | Material data**

|                           |                  |
|---------------------------|------------------|
| Coating locking           | Nickeled         |
| Coating of fitting        | nickel plated    |
| Locking material          | Zinc die-casting |
| Material screw connection | Zinc die-casting |

**Mechanical data | Mounting data**

|                 |                                       |
|-----------------|---------------------------------------|
| Mounting method | inserted, screwed, Shaking protection |
|-----------------|---------------------------------------|

**Environmental characteristics | Climatic**

|                                        |                            |
|----------------------------------------|----------------------------|
| Operating temperature min.             | -25 °C                     |
| Operating temperature max.             | 85 °C                      |
| Additional condition temperature range | depending on cable quality |

**Installation | Cable**

|                            |                               |
|----------------------------|-------------------------------|
| Cable identification       | 850                           |
| Jacket Color               | violet                        |
| Amount stranding           | 1                             |
| Stranding                  | 2 wires with 2 Filler twisted |
| Cable shielding (type)     | copper braid, tinned          |
| Cable shielding (coverage) | 70 %                          |
| Banding                    | Fleece, Foil                  |
| Filler                     | yes                           |
| wire arrangement           | red, green                    |

|                                                         |                                                      |
|---------------------------------------------------------|------------------------------------------------------|
| No. of bending cycles (C-track)                         | 2 Mio. @ 25 °C                                       |
| Cable weight                                            | 75,9 g/m                                             |
| Material jacket                                         | PVC                                                  |
| Freedom from ingredients (jacket)                       | lead-free, CFC-free                                  |
| Outer-diameter (jacket)                                 | 7,8 mm                                               |
| Tolerance outer diameter (sheath)                       | ± 5 %                                                |
| Amount wires                                            | 2                                                    |
| Outer diameter insulation                               | 2,55 mm                                              |
| Outer diameter tolerance core insulation                | ± 5 %                                                |
| Ingredient freeness wire insulation                     | lead-free, CFC-free, halogen-free                    |
| Amount strands (wire)                                   | 19                                                   |
| Diameter of single wires                                | 24 AWG                                               |
| Conductor crosssection (wire)                           | 24 AWG                                               |
| Material conductor wire                                 | Stranded copper wire, bare                           |
| Traversing distance (C-track)                           | 5 m @ 25 °C                                          |
| Current load capacity (standard)                        | to DIN VDE 0298-4                                    |
| Current load capacity min. wire                         | 4,5 A                                                |
| Electrical resistance line constant wire                | 78 Ω/km @ 20 °C                                      |
| Nominal voltage power AC max.                           | 30 V                                                 |
| Electric capacitance (power)                            | 30000 pF/km                                          |
| AC withstand voltage power (wire - shield)              | 1,5 kV @ 60 s                                        |
| Power frequency withstand voltage power (wire - jacket) | 1,5 kV @ 60 s                                        |
| AC withstand voltage power (wire - wire)                | 1,5 kV @ 60 s                                        |
| Min. operating temperature (static)                     | -25 °C                                               |
| Max. operating temperature (fixed)                      | 70 °C                                                |
| Operating temperature min. (dynamic)                    | -20 °C                                               |
| Operating temperature max. (dynamic)                    | 60 °C                                                |
| Flame resistance                                        | UL 1581 § 1090   UL 1581 § 1100 FT2   IEC 60332-2-2  |
| chemical resistance                                     | Good, application-related testing                    |
| Gasoline resistance                                     | Good, application-related testing                    |
| Oil resistance                                          | DIN EN 60811-404   Good, application-related testing |
| Bending radius (fixed)                                  | 7,5 x Outer diameter                                 |
| Bending radius (dynamic)                                | 12 x Outer diameter                                  |