

**MSUD valve plug A-18mm with cable**

PUR 4x0.75 gy UL/CSA 1.2m

MSUD

Form A (18 mm)

0...230 V AC/DC

without components




4-pole


PE at cable entry (180°)

Further cable lengths on request.

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link do produto](#)**Ilustração**



Produto pode diferir da imagem



|                                     |                   |
|-------------------------------------|-------------------|
| Cable length                        | 1,2 m             |
| Side 1                              |                   |
| Tightening torque                   | 0,4 Nm            |
| Mounting method                     | inserted, screwed |
| Family construction form            | MSUD A            |
| Thread                              | M3                |
| Material                            | PBT               |
| Degree of protection (EN IEC 60529) | IP67              |
| Dados comerciais                    |                   |
| ECLASS-6.0                          | 27279218          |
| ECLASS-7.0                          | 27279218          |
| ECLASS-8.0                          | 27279218          |
| ECLASS-9.0                          | 27060311          |
| ECLASS-10.1                         | 27060312          |
| ECLASS-11.1                         | 27060312          |
| ECLASS-12.0                         | 27060312          |
| ETIM-5.0                            | EC001855          |
| Classificação fiscal                | 85444290          |
| GTIN                                | 4048879190954     |
| Quantidade por embalagem            | 1                 |
| Electrical data   Supply            |                   |
| Operating voltage AC max.           | 230 V             |
| Operating voltage DC max.           | 230 V             |
| Current operating per contact max.  | 10 A              |
| Installation   Connection           |                   |
| Mounting set                        | M3                |
| Device protection   Electrical      |                   |
| Pollution Degree                    | 3                 |
| Rated surge voltage                 | 4 kV              |
| Material group (IEC 60664-1)        | I                 |
| Mechanical data   Material data     |                   |

As informações contidas nesta folha de dados foram elaboradas com o máximo cuidado.  
A falta de integridade, exatidão e atualização das informações é considerada negligência grave. versão: 19/04/2024

|                           |          |
|---------------------------|----------|
| Coating locking           | verzinkt |
| Coating of fitting        | verzinkt |
| Color housing             | black    |
| Material gasket           | PUR      |
| Locking material          | Steel    |
| Material screw connection | Steel    |

**Mechanical data | Mounting data**

|                 |                   |
|-----------------|-------------------|
| Mounting method | inserted, screwed |
|-----------------|-------------------|

**Environmental characteristics | Climatic**

|                                        |                            |
|----------------------------------------|----------------------------|
| Operating temperature min.             | -25 °C                     |
| Operating temperature max.             | 85 °C                      |
| Additional condition temperature range | depending on cable quality |

**Installation | Cable**

|                                          |                                                  |
|------------------------------------------|--------------------------------------------------|
| Cable identification                     | 227                                              |
| Cable Type                               | 2                                                |
| Printing color of wire insulation        | white (isolation black)                          |
| Jacket Color                             | gray                                             |
| Type of Certificate                      | cURus                                            |
| Amount stranding                         | 1                                                |
| Stranding                                | 4 wires twisted                                  |
| wire arrangement                         | black 1, black 2, black 3, green-yellow          |
| No. of bending cycles (C-track)          | 2 Mio. @ 25 °C                                   |
| Cable weight                             | 74,8 g/m                                         |
| Material jacket                          | PUR                                              |
| Shore hardness jacket                    | 85 ± 5 Shore A                                   |
| Freedom from ingredients (jacket)        | lead-free, cadmium-free, CFC-free, silicone-free |
| Outer-diameter (jacket)                  | 7 mm                                             |
| Tolerance outer diameter (sheath)        | ± 5 %                                            |
| Material inner jacket                    | PVC                                              |
| Color (inner jacket)                     | yellow                                           |
| Material wire insulation                 | PVC                                              |
| Amount wires                             | 4                                                |
| Outer diameter insulation                | 1,8 mm                                           |
| Outer diameter tolerance core insulation | ± 5 %                                            |
| Shore hardness wire insulation           | 43 ± 5 Shore D                                   |
| Ingredient freeness wire insulation      | lead-free, cadmium-free, CFC-free, silicone-free |
| Printing color of wire insulation        | white (isolation black)                          |
| Amount strands (wire)                    | 42                                               |
| Diameter of single wires                 | 0,15 mm                                          |
| Conductor crosssection (wire)            | 0,75 mm²                                         |
| Material conductor wire                  | Stranded copper wire, bare                       |
| Conductor type (wire)                    | strand class 6                                   |
| Electrical function wire                 | Signal                                           |
| Traversing distance (C-track)            | 5 m @ 25 °C   horizontal                         |
| Current load capacity (standard)         | to DIN VDE 0298-4                                |
| Current load capacity min. wire          | 9,6 A                                            |
| Electrical function wire                 | Signal                                           |
| Electrical resistance line constant wire | 26 Ω/km @ 20 °C                                  |
| Nominal voltage power AC max.            | 300 V                                            |
| Min. operating temperature (static)      | -30 °C                                           |
| Max. operating temperature (fixed)       | 80 °C                                            |
| Operating temperature min. (dynamic)     | -5 °C                                            |
| Operating temperature max. (dynamic)     | 80 °C                                            |

|                          |                                   |
|--------------------------|-----------------------------------|
| chemical resistance      | Good, application-related testing |
| Gasoline resistance      | Good, application-related testing |
| Oil resistance           | DIN EN 60811-404                  |
| Bending radius (fixed)   | 10 x Outer diameter               |
| Bending radius (dynamic) | 15 x Outer diameter               |