





M12 female 90° A-cod. with cable shielded

PUR 5x0.34 shielded gy 35m

Female 90°  
M12, 5-pole  
shielded  
with cable sleeves  
Plastic housings with good resistance against chemicals and oils.  
The resistance to aggressive media should be individually tested for your application. Further details on request.  
Further cable lengths on request.

Link do produto

Ilustração



Produto pode diferir da imagem



|                   |        |
|-------------------|--------|
| Cable length      | 35 m   |
| Side 1            |        |
| Tightening torque | 0,6 Nm |

|                                     |                   |
|-------------------------------------|-------------------|
| Mounting method                     | inserted, screwed |
| Coating contact                     | gold plated       |
| Family construction form            | M12               |
| Thread                              | M12 x 1           |
| Coding                              | A                 |
| Material contact                    | Copper alloy      |
| Material                            | PUR               |
| No. of poles                        | 5                 |
| Width across flats                  | SW13              |
| Degree of protection (EN IEC 60529) | IP65, IP66K, IP67 |

**Side 2**

|                           |             |
|---------------------------|-------------|
| Stripping length (jacket) | 20 mm       |
| Coating contact           | gold plated |

**Dados comerciais**

|                          |               |
|--------------------------|---------------|
| ECLASS-6.0               | 27279218      |
| ECLASS-7.0               | 27279218      |
| ECLASS-8.0               | 27279218      |
| ECLASS-9.0               | 27060311      |
| ECLASS-10.1              | 27060311      |
| ECLASS-11.1              | 27060311      |
| ECLASS-12.0              | 27060311      |
| ETIM-5.0                 | EC001855      |
| Classificação fiscal     | 85444290      |
| GTIN                     | 4048879291767 |
| Quantidade por embalagem | 1             |

**Electrical data | Supply**

|                                    |      |
|------------------------------------|------|
| Operating voltage AC max.          | 60 V |
| Operating voltage DC max.          | 60 V |
| Current operating per contact max. | 4 A  |

**Diagnostics**

|                       |    |
|-----------------------|----|
| Status indication LED | no |
|-----------------------|----|

**Installation | Connection**

|                           |         |
|---------------------------|---------|
| Stripping length (jacket) | 20 mm   |
| Mounting set              | M12 x 1 |

**Device protection | Electrical**

|                                        |                   |
|----------------------------------------|-------------------|
| Additional condition protection degree | inserted, screwed |
| Pollution Degree                       | 3                 |
| Rated surge voltage                    | 1,5 kV            |
| Material group (IEC 60664-1)           | I                 |

**Mechanical data**

|                             |         |
|-----------------------------|---------|
| Contour for corrugated hose | without |
|-----------------------------|---------|

**Mechanical data | Material data**

|                           |                  |
|---------------------------|------------------|
| Coating locking           | Nickeled         |
| Coating of fitting        | nickel plated    |
| Material gasket           | FKM              |
| Locking material          | Zinc die-casting |
| Material screw connection | Zinc die-casting |

**Mechanical data | Mounting data**

|                 |                                       |
|-----------------|---------------------------------------|
| Mounting method | inserted, screwed, Shaking protection |
|-----------------|---------------------------------------|

**Environmental characteristics | Climatic**

|                                        |                            |
|----------------------------------------|----------------------------|
| Operating temperature min.             | -25 °C                     |
| Operating temperature max.             | 85 °C                      |
| Additional condition temperature range | depending on cable quality |

#### Important installation notes

|                        |                                                                                                                                                       |
|------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|
| Note on strain relief  | Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.                                                   |
| Note on bending radius | <b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces. |

#### Conformity

|                  |                          |
|------------------|--------------------------|
| Product standard | DIN EN 61076-2-101 (M12) |
|------------------|--------------------------|

#### Installation | Cable

|                                                   |                                                     |
|---------------------------------------------------|-----------------------------------------------------|
| Cable identification                              | 349                                                 |
| Jacket Color                                      | gray                                                |
| Amount stranding                                  | 1                                                   |
| Stranding                                         | 5 wires around Core filler twisted                  |
| Cable shielding (type)                            | copper braid, tinned                                |
| Cable shielding (coverage)                        | 85 %                                                |
| Banding                                           | Fleece, Foil                                        |
| Filler                                            | yes                                                 |
| wire arrangement                                  | brown, black, blue, white, green-yellow             |
| Traversing distance (C-track)                     | 5 m @ 25 °C                                         |
| Cable weight                                      | 59,4 g/m                                            |
| Material jacket                                   | PUR                                                 |
| Shore hardness jacket                             | 85 ± 5 Shore A                                      |
| Freedom from ingredients (jacket)                 | lead-free, cadmium-free, CFC-free, halogen-free     |
| Outer-diameter (jacket)                           | 5,9 mm                                              |
| Tolerance outer diameter (sheath)                 | ± 5 %                                               |
| Material inner jacket                             | PVC                                                 |
| Color (inner jacket)                              | gray                                                |
| Material wire insulation                          | PVC                                                 |
| Amount wires                                      | 5                                                   |
| Outer diameter insulation                         | 1,45 mm                                             |
| Outer diameter tolerance core insulation          | ± 5 %                                               |
| Shore hardness wire insulation                    | 85 ± 5 Shore A                                      |
| Material properties wire insulation               | good machinability                                  |
| Ingredient freeness wire insulation               | lead-free, cadmium-free, CFC-free, silicone-free    |
| Amount strands (wire)                             | 42                                                  |
| Diameter of single wires                          | 0,1 mm                                              |
| Conductor crosssection (wire)                     | 0,34 mm²                                            |
| Material conductor wire                           | Stranded copper wire, bare                          |
| Conductor type (wire)                             | strand class 6                                      |
| Max. rated voltage (conductor - conductor)        | 350 V                                               |
| Max. rated voltage (conductor - ground)           | 300 V                                               |
| Current load capacity (standard)                  | to DIN VDE 0298-4                                   |
| Current load capacity min. wire                   | 4,5 A                                               |
| Electrical resistance line constant wire          | 57 Ω/km @ 20 °C                                     |
| AC withstand voltage (wire - wire)                | 2 kV @ 60 s                                         |
| Power frequency withstand voltage (wire - jacket) | 2 kV @ 60 s                                         |
| AC withstand voltage (wire - shield)              | 1,5 kV @ 60 s                                       |
| Min. operating temperature (static)               | -40 °C                                              |
| Max. operating temperature (fixed)                | 80 °C                                               |
| Operating temperature min. (dynamic)              | -5 °C                                               |
| Operating temperature max. (dynamic)              | 70 °C                                               |
| Flame resistance                                  | IEC 60332-2-2   UL 1581 § 1090   UL 1581 § 1100 FT2 |

As informações contidas nesta folha de dados foram elaboradas com o máximo cuidado.

A falta de integridade, exatidão e atualização das informações é considerada negligência grave. versão: 13/05/2024

|                          |                                                      |
|--------------------------|------------------------------------------------------|
| chemical resistance      | Good, application-related testing                    |
| Gasoline resistance      | Good, application-related testing                    |
| Oil resistance           | DIN EN 60811-404   Good, application-related testing |
| Bending radius (fixed)   | 10 x Outer diameter                                  |
| Bending radius (dynamic) | 15 x Outer diameter                                  |
| Travel speed (C-track)   | 0,1 Mio. @ 25 °C                                     |